

Baroque™ Customline®

PERFORMANCE SERIES MINERAL FIBER CEILING



Specification Sheet

Features & Benefits:

- Three dramatic geometric designs with 100% non-directional fissured pattern.
- Clean 3-dimensional scoring, free of fissures or pin perforations.
- Features deep shadow face scoring.
- Product's deep scoring complements the suspension system, masking the metal grid.
- No added formaldehyde.

Applications:



- Hospitality
- Retail
- Offices
- Education
- Healthcare
- Restaurants

See reverse for additional product specifications.


Attributes:

ITEM NUMBER	NOMINAL SIZE (Inches)	EDGE DETAIL	UL CLASSIFIED		LR	RECYCLED CONTENT %
			NRC	CAC		
SAFETONE® CLASS A						
BQCL-224	24 x 48 x 3/4	Reveal	0.60	38	0.83	36-45
BQCLN-224	24 x 48 x 3/4	Narrow Reveal	0.60	38	0.83	36-45
BQCL-448	24 x 48 x 3/4	Reveal	0.50	38	0.83	36-45
BQCLN-448	24 x 48 x 3/4	Narrow Reveal	0.50	38	0.83	36-45
BQCL-812	24 x 48 x 3/4	Reveal	0.50	38	0.83	36-45
BQCLN-812	24 x 48 x 3/4	Narrow Reveal	0.50	38	0.83	36-45
PROTECTONE® (For specific UL fire resistant time-rated assemblies)						
PBQCL-224	24 x 48 x 3/4	Reveal	0.50	40	0.83	47

ASTM E 1264 Classification: Type III, Form 2, Pattern C D K




Scoring Options:



24" x 48"
224



24" x 48"
448




24" x 48"
812




BioShield™ Option
Mild and mildew guard
available as an option.

Edge Details:



REVEAL EDGE
(Beveled) 1/4" Grid



NARROW REVEAL EDGE
(Beveled) 1/4" Grid



Product Specification Details

Acoustical Ceilings

09 51 00

PART 2: PRODUCTS

2.1 GENERAL

Provide Acoustical Ceiling Material manufactured to meet requirements of this specification in accordance with ASTM E 1264.

2.2 MATERIALS

Acoustical Ceiling Units:

1. Type III
2. Form 2
3. Pattern [C] [D] [K]
4. Non-directional fissured and perforated Baroque™ pattern surface scored to simulate [two 24" x 24"] [four 6" x 48"] [eight 12" x 12"] lay-in panels
5. Size 3/4" thick x 24" x 48"
6. Edge Detail [Reveal] [Narrow Reveal]
7. Noise Reduction Coefficient (NRC) [0.50] [0.60]
8. Ceiling Attenuation Class (CAC) [38] [40]
9. Light Reflectance Coefficient (LR) 0.83
10. Recycled Content [36-45] [47]
11. Color White
12. Flame Spread Classification (ASTM E 84, CAN/ULC-S102M) Class A
13. Underwriters Laboratories Inc. Fire Resistance (ASTM E 119, CAN/ULC-S101M) Time-Rated Assembly* [G208] [G218] [G248] [G255]
14. Manufacturer, subject to compliance with requirements of this specification, CertainTeed Ceilings
15. Product Name [Baroque™ Customline®] [Protectone® Baroque™ Customline®]

* Relevant to Protectone® only. Refer to UL Fire Resistant Directory for specific design information.

Distributed by:

Characteristics, properties or performance of materials or systems manufactured by CertainTeed herein described are derived from data obtained under controlled test conditions. CertainTeed makes no warranties, express or implied, as to their characteristics, properties or performance under any variations from such conditions in actual construction. CertainTeed assumes no responsibility for the effects of structural movement.

NOTICE: The information in this document is subject to change without notice. CertainTeed assumes no responsibility for any errors that may inadvertently appear in this document.
