

Specification Sheet

Features & Benefits:

- 100% non-directional fissured pattern.
- Variety of edge detail options and panel sizes.
- No added formaldehyde.

See reverse for additional product specifications.


Applications:

- Hospitality
- Retail
- Offices
- Education
- Healthcare
- Restaurants


Attributes:

ITEM NUMBER	NOMINAL SIZE (Inches)	EDGE DETAIL	UL CLASSIFIED		LR	RECYCLED CONTENT %	
			NRC	CAC		POST	PRE
SAFETONE® CLASS A							
BET-150	24 x 24 x 5/8	Narrow Reveal	0.60	33	0.83	18	18-27
BET-154	24 x 24 x 5/8	Reveal	0.60	33	0.83	18	18-27
BET-157	24 x 24 x 5/8	Trim	0.60	33	0.83	18	18-27
BET-194	24 x 48 x 5/8	Reveal	0.60	35	0.83	18	18-27
BET-197	24 x 48 x 5/8	Trim	0.60	35	0.83	18	18-27
BET-2067	24 x 60 x 5/8	Trim	0.60	35	0.83	18	18-27
PROTECTONE® (For specific UL fire resistant time-rated assemblies)							
PBT-154	24 x 24 x 5/8	Reveal	0.55	35	0.83	9	38
PBT-157	24 x 24 x 5/8	Trim	0.55	35	0.83	9	38
PBT-197	24 x 48 x 5/8	Trim	0.55	40	0.83	9	38


ASTM E 1264 Classification: Type III, Form 2, Pattern C D




Edge Details:




TRIM EDGE
(Square) 15/16" Grid



REVEAL EDGE
(Beveled) 15/16" Grid



NARROW REVEAL EDGE
(Corner Bevel) 9/16" Grid



NARROW REVEAL EDGE
(Corner Bevel)
9/16" Grid (Bolt Slot)



Product Specification Details

Acoustical Ceilings

09 51 00

PART 2: PRODUCTS

2.1 GENERAL

Provide Acoustical Ceiling Material manufactured to meet requirements of this specification in accordance with ASTM E 1264.

2.2 MATERIALS

Acoustical Ceiling Units:

1. Type III
2. Form 2
3. Pattern [C] [D]
4. Non-directional fissured and perforated wet-felted lay-in panels and tile.
5. Size 5/8" thick x [24" x 24"] [24" x 48"]
6. Edge Detail [Trim (Square)] [Reveal] [Narrow Reveal]
7. Noise Reduction Coefficient (NRC) [0.55] [0.60]
8. Ceiling Attenuation Class (CAC) [33] [35] [40]
9. Light Reflectance Coefficient (LR) 0.83
10. Recycled Content [9-18 post] [18-38 pre]
11. Color White
12. Flame Spread Classification (ASTM E 84, CAN/ULC-S102M) Class A
13. Underwriters Laboratories Inc. Fire-Resistance (ASTM E 119, CAN/ULC-S101M) Time-Rated Assembly* [D203] [D205] [G208] [G218] [G248] [G255] [L201] [P204] [P259] [P260] [P261] [P262] [P264]
14. Manufacturer, subject to compliance with requirements of this specification, CertainTeed Ceilings
15. Product Name [Baroque™] [Protectone® Baroque™]

* Relevant to Protectone® only. Refer to UL Fire Resistant Directory for specific design information.

Suspension Systems:

1. Profile [9/16" Face] [15/16" Face]
2. Manufacturer CertainTeed Ceilings Systems
3. Product Names [15/16" Classic Stab] [15/16" Classic Hook] [15/16" Classic Environmental Stab] [15/16" Classic Aluminum Capped Stab] [15/16" Classic Aluminum Capped Hook] [9/16" Elite Narrow Stab] [9/16" Smoothline Bolt Slot]
4. Warranty 15-year Limited Warranty when CertainTeed suspension system is installed together with any CertainTeed ceiling panel

Characteristics, properties or performance of materials or systems manufactured by CertainTeed herein described are derived from data obtained under controlled test conditions. CertainTeed makes no warranties, express or implied, as to their characteristics, properties or performance under any variations from such conditions in actual construction. CertainTeed assumes no responsibility for the effects of structural movement.

NOTICE: The information in this document is subject to change without notice. CertainTeed assumes no responsibility for any errors that may inadvertently appear in this document.