




Martin Yale® 1812 & 2051 Paper Folders



1812 & 2051

- Variable speed folding machines allowing you to switch from one paper weight to another without making any adjustments, saving time between folding jobs
- Feed table has a capacity of 500 sheets of 20lb bond paper
- Straightforward display for manual fold and speed selection
- Fold tables are fully enclosed for quieter operation
- Automatically shuts off when fold job is complete

Fold Types:



Martin Yale® Model #		1812	2051
Benchmark Speed	sheets/hr	5,000-12,000	3,000-15,000
Standard paper size	inch cm	2.5 x 5.2 to 12 x 18 A3, A4, A5, Custom	2.5 x 5.2 to 12 x 18 A3, A4, A5, Custom
Paper Weight		68 gsm to 166 gsm 18# Bond to 90# Index	68 gsm to 166 gsm 18# Bond to 90# Index
Manual Paper Feed	up to sheets	N/A	N/A
Feed Tray Capacity	up to sheets	500	500
Power	volts	115/230	115/230
Dimensions	W x D x H approx. inch cm	25 x 22.2 x 17.8 64 x 56 x 45	25 x 22.2 x 17.8 64 x 56 x 45
Weight	approx. ounces/lbs	102 lbs.	102 lbs.

Martin Yale Industries, LLC
251 Wedcor Avenue Wabash, IN 46992
Phone: 800.225.5644 Fax: 260.563.4575
www.martinyale.com

1812

Folds

2.5" x 5.2" to 12" x 18"

Benchmark Speed up to:

12,000 sheets per/hr

Paper Weights

18# Bond to 90# Index

60 gsm to 166 gsm

2051

Folds

2.5" x 5.2" to 12" x 18"

Benchmark Speed up to:

15,000 sheets per/hr

Paper Weights

18# Bond to 90# Index

68 gsm to 166 gsm