Small Office Shredder





Office Shredder with its ability to get the job done quickly and easily with minimal effort. Small offices or teams of employees will benefit from the ease of use and quiet operation of this small to mid-size shredder. It's perfect for destroying personnel records, client proposals and tax information. Dahle's 40306 is built with a 10 1/4" feed opening to accommodate both letter and legal size paper with ease. This strip-cut machine offers a 1/4" particle size and is able to shred to security level P-2 standards. All

will take care of the rest.

This shredder features Automatic On/Off operation that uses an electronic sensor to turn the machine on. All you have to do is position your document in the feed opening and the shredder will take care of the rest. Bag Full Auto Off is another con-

vou need to do is decide what document to

shred and this Dahle Small Office shredder

Proficiency best describes this Dahle Small

venient function that notifies you when the shred bag is full and needs to be changed. It's these state-of-the-art features that saves you time and takes the burden out of shredding your documents.

Energy conservation continues to be a top priority at Dahle. Each shredder comes equipped with the revolutionary SmartPower Energy Management System. This multistage system reduces power consumption after ten minutes of sitting idle (sleep mode), and completely powers down after an additional 20 minutes of inactivity. Dahle SmartPower will appeal to those interested in conserving energy as well as reducing electrical costs.

Dahle's shredders are German Engineered using the latest technology and finest materials. The end result is a quality machine and peace of mind in knowing your Dahle shredder will provide many years of trouble free operation.

Features

• Feed Opening: 10 1/4"

• Sheet Capacity: 20/24

• Shred Size: 1/4"

• Security Level: P-2

• SmartPower Management

• German Engineered



This Dahle Professional shredder with built in user-friendly opening for CD/DVD destruction.



all of the shredder's functions such as cutting cylinders, a steel chain & gears



power up, reverse, and continuous run. connect the two for maximum capacity.

| Sp | Specifications | | | | | | | | | | | | | | | |
|-------|----------------|-----------------------|-------------------|------------|-----------------|--------|------------------|---------------|----------|---|------------------------|--|-----|------------|-----------------------|--------|
| Model | Feed Width | Capacity #20 / #16 | Security Level | Shred Size | Waste Volume | Speed | Decibel Level | Staples/Clips | CDs/DVDs | | res/Capab CleanTEC® | | ESP | Auto Oiler | Dimensions | Weight |
| 40306 | 10 1/4" | 20 / 24 | P-2 | 1/4" | 23 gal | 14 f/m | 47 dB | • | • | • | | | | | 34 ¼" x 21 ½" x 17 ½" | 88 lbs |

All performance data has been established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.





Authorized Dealer