



No.:

Date: 17-DEC-2012

Customer :

TECHNICAL PROPOSAL

Three-phase induction motor - Squirrel cage rotor

Product line : W22 NEMA Premium - Roller Bearings

Catalog Number : 45012ET3GRB586/7-W22

List Price : \$62,251

Notes:

Performed by:

Checked:



No.:

Date: 17-DEC-2012

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 NEMA Premium - Roller Bearings

Frame : 586/7T
Output : 450 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1190
Slip : 0.83 %
Voltage : 460 V
Rated current : 532 A
Locked rotor current : 3300 A
Locked rotor current (I_L/I_n) : 6.2
No-load current : 210 A
Full load torque : 1959 lb.ft
Locked rotor torque : 210 %
Breakdown torque : 210 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 26 s (hot)
Service factor : 1.00
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000
Degree of Protection : IP55
Approximate weight : 4384 lb
Moment of inertia : 367.54 sq.ft.lb
Noise level : 77 dB(A)

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	NU-322 C3	6319 C3	100%	0.81	96.2
Regreasing interval	7000 h	13000 h	75%	0.77	96.2
Grease amount	60 g	45 g	50%	0.67	95.8

Notes:

Performed by


Checked



No.:

Date: 17-DEC-2012

PERFORMANCE CURVES RELATED TO RATED OUTPUT Three-phase induction motor - Squirrel cage rotor



Customer :
Product line : W22 NEMA Premium - Roller Bearings

Frame : 586/7T	Locked rotor current (I _l /I _n) : 6.2
Output : 450 HP	Duty cycle : S1
Frequency : 60 Hz	Service factor : 1.00
Full load speed : 1190	Design : B
Voltage : 460 V	Locked rotor torque : 210 %
Rated current : 532 A	Breakdown torque : 210 %
Insulation class : F	

Notes:

Performed by


Checked



No.:

Date: 17-DEC-2012

CHARACTERISTIC CURVES RELATED TO SPEED Three-phase induction motor - Squirrel cage rotor



Customer :
Product line : W22 NEMA Premium - Roller Bearings

Frame	: 586/7T	Locked rotor current (I _l /I _n)	: 6.2
Output	: 450 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.00
Full load speed	: 1190	Design	: B
Voltage	: 460 V	Locked rotor torque	: 210 %
Rated current	: 532 A	Breakdown torque	: 210 %
Insulation class	: F		

Notes:

Performed by

Checked