


Panels/Accessories  
Filing/Storage/Table Bases  
Privacy Screens



# ProPanels



Light Gray/Slate


ProPanels are designed to help maintain personal space in settings with multiple workstations.

ProPanels divide and organize private work areas, yet still allow opportunity for discussion and collaboration. Customization is a cinch with numerous size and layout options. Manage the open office environment with ProPanels.




Harvest Tan/Taupe

## Fabric Options



Harvest Tan/  
Taupe  
(HT)



Light Gray/  
Slate  
(LG)



2-Way Connector

# Panels



Light Gray/Slate



Harvest Tan/Taupe

- ☑ Durable extruded frames trimmed with fabric-covered panels
- ☑ Panel interiors have a rigid engineered wood frame with a combination of hardboard/corrugated interiors
- ☑ All panels include straight-line connection hardware to mount to similar height panel
- ☑ Panels include adjustable levelers
- ☑ Meets ANSI/BIFMA standards for safety and performance
- ☑ Commercial quality backed by BBF 10-year Warranty



Wall Kit



Foot Kit




42"H x 36"W  
Panel  
PP42536-03 HT  
PP42736-03 LG




42"H x 48"W  
Panel  
PP42548-03 HT  
PP42748-03 LG




42"H x 60"W  
Panel  
PP42560-03 HT  
PP42760-03 LG



66"H x 36"W  
Panel  
PP66536-03 HT  
PP66736-03 LG



66"H x 48"W  
Panel  
PP66548-03 HT  
PP66748-03 LG



66"H x 60"W  
Panel  
PP66560-03 HT  
PP66760-03 LG



Wall  
Starter Kit  
PH99501-03 TA  
PP84901-03 SL




X Connector  
with 66H Post  
PH99568-03 TA  
PP84714-03 SL



X Connector  
with 42H Post  
PH99543-03 TA  
PP99743-03 SL




High/Low Connectors  
with 42H Post  
PH99590-03 TA  
PH99790-03 SL




High/Low  
3-Way Connector  
PH99593-03 TA  
PH99793-03 SL



Foot  
Kit  
PH99599-03 HT  
PP84999-03 LG



2-Way or 3-Way  
Connector  
(for 66"H Panels)  
PH99566-03 TA  
PH99766-03 SL



2-Way or 3-Way  
Connector  
(for 42"H Panels)  
PH99542-03 TA  
PH99742-03 SL

# Accessories

See BBF Pricer for compatibility with collections



Deluxe Articulating Keyboard Tray (Black finish)  
Long Track **AC99889**  
Med Track **AC99887**  
Short Track **AC99888**



Universal Keyboard Tray (Galaxy finish)  
**AC99808-03**



Multi-purpose Drawer w/Drop Front (Black finish)  
**AC99855-03**



Data/Power HUB (Satin Nickel finish)  
**AC99840-03**



Monitor Arm w/Post (Satin Nickel finish)  
**AC99830-03**



Universal Grommet Kit  
**AC99845**



Articulating Keyboard Tray (Black finish)  
**AC99801-03**



Task Light (Pewter finish)  
**WC8065C-03**



Pencil Drawer (Black finish)  
**AC99850**



CPU Holder (Black finish)  
**AC99820-03**



Universal Wire Tray Kit  
**AC99865**



Universal Door Lock Kit  
**AC99823** (Chrome)  
**AC99826** (Black)



Articulating Keyboard Tray



Monitor Arm



Data/Power HUB

## Deluxe Articulating Keyboard Tray

- Position indicators for both height and tilt
- Soft-touch wheel allows convenient one-handed tilt adjustment
- Total vertical range of 8" (3" above to 5" below work surface)
- Total horizontal (in/out travel) range of 15"
- Capable of 30° of tilt adjustment (20° negative to 10° positive)
- Positive tilt lock-out pin included
- "Lift and Release" height adjustment
- Removable wrist rest with easy-to-clean cover
- Mouse pad included
- Additional wire management clips and mouse fence included

## Articulating Keyboard Tray

- Retracts under desk surface when not in use
- 5.3" height adjustable range (knobless)
- Capable of 27 degrees of tilt adjustment (17° negative to 10° positive)
- 15" of forward-backward travel
- Swivels 180° left and right

## Universal Keyboard Tray

- Holds keyboard and mouse

## Task Light

- Mounts on most hutches
- 8' cord length

## Multi-purpose Drawer w/Drop Front

- Multi-function can be used as a keyboard drawer, laptop docking station, or pencil drawer
- Drop design drawer front
- Ventilated bottom shelf allows air flow

## Pencil Drawer

- Sloped front for reduced visibility and visual appeal
- Height-adjustable brackets
- ¾-extension ball bearing slides

## Data/Power Hub

- Integrated power surge protection
- Front of unit contains:
  - Two 120 AC power outlets
  - One phone jack
  - One CAT5 Ethernet and one firewire port
  - Two USB ports
- Rear of unit contains:
  - One matching data port
  - One phone jack
  - One USB port
- 10' heavy duty grounded power cord

## CPU Holder (for Quantum only)

- Mounts on underside of any work surfaces except bridges
- Pivots 360°, extends or retracts on ball bearing slides within a 7" range
- Fits CPUs up to 20.5"H x 8.25"W and weighing up to 50 lbs.

## Monitor Arm w/Post

- Mounts on any 3" wire management grommet
- Allows monitor to tilt, swivel and rotate
- Will accommodate most flat panel monitors up to 20" with Vesa 100 mm mounting holes
- Has steel post with aluminum arm and 13" height adjustment range

## Universal Grommet Kit

- Allows for easy routing of cables through desk top
- Includes 2 grommets per kit

## Universal Wire Tray Kit

- Channels provides a versatile cable management system
- Set consists of two trays

## Universal Door Lock Kit


- Different lock core/key sets available to allow multiple office settings to have their own key for increased security

# Bookcases/Height Adjustable Table Bases




## BBF Bookcases

- ☑ Adjustable shelves for storage flexibility
- ☑ Wall attachment hardware included
- ☑ Ideal for books or miscellaneous office supplies
- ☑ Meets ANSI/BIFMA standards for safety and performance in place at time of manufacture
- ☑ Commercial Quality backed by a 10 Year Warranty
- ☑ American Made




72H  
5 Shelf Bookcase

- BK7236CS
- BK7236MR
- BK7236AC
- BK7236HC
- BK7236NC




66H 5 Shelf  
Narrow Bookcase

- BK6618CS
- BK6618MR
- BK6618AC
- BK6618HC
- BK6618NC



66H  
5 Shelf Bookcase

- BK6636CS
- BK6636MR
- BK6636AC
- BK6636HC
- BK6636NC



48H  
3 Shelf Bookcase

- BK4836CS
- BK4836MR
- BK4836AC
- BK4836HC
- BK4836NC



30H  
2 Shelf Bookcase

- BK3036CS
- BK3036MR
- BK3036AC
- BK3036HC
- BK3036NC



Harvest Cherry  
(CS)



Mocha Cherry  
(MR)



Natural Cherry  
(NC)



Natural Maple  
(AC)



Hansen Cherry  
(HC)


## Height Adjustable Table Bases

- ☑ Height Adjustment range from 23H up to 49H
- ☑ Width adjustment range from 43W to 71W
- ☑ Weight capacity up to 200 lbs
- ☑ Four memory presets with soft touch start and stop
- ☑ Meets ANSI/BIFMA standards for safety and performance in place at time of manufacture
- ☑ Commercial Quality backed by a 5 Year Warranty



24D Height  
Adjustable Table Base  
Metallic Gray

HATB24DGM-03




30D Height  
Adjustable Table Base  
Metallic Gray

HATB30DGM-03



24D Height  
Adjustable Table Base  
Black

HATB24DBL-03



30D Height  
Adjustable Table Base  
Black

HATB30DBL-03

# Privacy Screens



Desk Mounted, Stationary and Mobile Freestanding Screens shown with Momentum

Support collaboration and concentration with  
Bush Business Furniture Privacy Screens.



Desk Mounted Frosted Acrylic Screens



Freestanding White Board Screens

Privacy screens offer space division that help address visual distractions and improve productivity. Quickly and easily create workstations, cubicles, study areas and more with these configurable screen options.

### Desk Mounted Screens

- ☑ Mounts to Desks or Returns temporarily or permanently
- ☑ Clamp Mount method prevents damage to work surface
- ☑ Adjustable clamps fit tables ranging from 5/8 to 2 inches thick
- ☑ At 1/8 in thick, Frosted Acrylic surface is 17% stronger than glass
- ☑ Acrylic surface provides light filtering privacy while concealing fingerprints and scratches



**42W Desktop Privacy Screen**  
PSP142FR  
39.49"W x 17.72"H



**48W Desktop Privacy Screen**  
PSP148FR  
45.67"W x 17.72"H



**60W Desktop Privacy Screen**  
PSP160FR  
57.52"W x 17.72"H



**66W Desktop Privacy Screen**  
PSP166FR  
64.96"W x 17.72"H



**72W Desktop Privacy Screen**  
PSP172FR  
69.09"W x 17.72"H



**Top Mount Hardware (Set of 3)**  
PSP202SV



**24W Side Desktop Privacy Screen**  
PSP124FR  
21.42"W x 17.72"H



**30W Side Desktop Privacy Screen**  
PSP130FR  
28.82"W x 17.72"H

### Freestanding Screens

- ☑ White Surface is non-ghosting and compatible with most dry or wet erase markers
- ☑ Nesting design allows for space-saving storage
- ☑ Durable, light weight and easy to move
- ☑ Product core is constructed using a sound absorbing material to reduce noise levels



**Freestanding White Board Screen with Stationary Base**  
PSP335WHK  
35.25"W x 62.4"H



**Freestanding White Board Screen with Wheeled Base**  
PSP435WHK  
35.25"W x 62.4"H



**Freestanding Frosted Acrylic Screen with Stationary Base**  
PSP535FRK  
35.24"W x 62.4"H



**Freestanding Frosted Acrylic Screen with Wheeled Base**  
PSP635FRK  
35.24"W x 62.4"H



**Accessory Board Clips for Freestanding Screens**  
PSP102CL

### All Screens

- ☑ All metal parts are made of anodized aluminum for durability and a sleek appearance
- ☑ Commercial quality backed by 5-Year warranty
- ☑ Meets ANSI/BIFMA standards for safety and performance
- ☑ American Made

**Coordinates with Bush Business Furniture (BBF) Collections:**

**Series C, Series C Elite, Realize, 300 Series, Series A and Momentum desk products.**

# Metal Filing



2-Drawer  
Vertical Metal File  
**80FV2XX**



36"W 2-Drawer  
Lateral Metal File  
**80FL236XX**



36"W 4-Drawer  
Lateral Metal File  
**80FL436XX**

## Synchronize 1000V (Vertical)

- ☑ 3/4-extension drawers with ball bearing slides
- ☑ Barrel-style lock mechanism with removable core, comes standard with two keys
- ☑ Drawers accommodate letter-sized files
- ☑ Designed to fit underneath a desk
- ☑ Removable drawer fronts
- ☑ Aluminum drawer pulls with thumb-activated drawer latch
- ☑ Aluminum label holders are standard
- ☑ Galvanized steel protects against rust and corrosion
- ☑ Meets ANSI/BIFMA test standards for commercial office furniture in place at time of manufacture
- ☑ Limited Lifetime Warranty

## Synchronize 1000L (Lateral)

- ☑ One removable core lock for both drawers, with dual locking bars for added security
- ☑ Anti-tip mechanism prevents more than one drawer from opening at a time
- ☑ Removable drawer fronts
- ☑ Full-extension drawers with ball bearing slides
- ☑ Drawers accommodate letter, legal and A4-sized files
- ☑ Leveling glides compensate for uneven floors
- ☑ Magnetic drawer contents identifier
- ☑ Fully finished bases
- ☑ Meets ANSI/BIFMA test standards for commercial office furniture in place at time of manufacture
- ☑ Limited Lifetime Warranty

## Finish Options

(both filing collections)



Black  
(BK)



Putty  
(PY)