

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

All anodized finishes have white integral flange ring as standard.

INSTALLATION

Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.


LISTING

U.L. Listed to U.S. and Canadian safety standards.


Damp location listed.

6" Full Reflector Trim

702



OPEN
Narrow Flange



Specifications

Height: 6-1/8 (15.6)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **702 TOR**

702	
Series	Finish
702	(blank) White

TOR
Mounting method
TOR Torsion springs

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6
		65 BR30	L7X, L7XR, LC6
	Fluorescent	13DTT	L7XF, L7XFR
		26TRT	L7XF, L7XFR

