



ST-900SD

1.5" SUBMERSIBLE PUMP



SPECIFICATIONS

1.5" SIDE DISCHARGE TRASH SUBMERSIBLE W/ FLOAT

1 1/4 HP, 115V, 1100W
TETHERED FLOAT SWITCH
4095 GAL /HR CAPACITY
36 FT MAX DELIVERY HEIGHT
16.5 FT MAX SUBMERSIBLE DEPTH
1.4" MAXIMUM SOLID HANDLING
COPPER WINDINGS
MECHANICAL SEAL
25 FT CORD
STAINLESS STEEL BODY

PART# ST-900SD

PUMP
WARRANTY

