

SPEAKMAN®

SE-609

COMBINATION SHOWER & EYE/FACE WASH



DESCRIPTION

The SE-609 Safe-T-Zone® freeze protected combination unit features the SE-400 eye/face wash with six aerated sprays and rectangular stainless steel bowl combined on a powder coated galvanized steel stanchion with an impeller action deluge showerhead. Supplies activated by frost-proof hydrants.

SPECIFICATIONS

- Showerhead:** 8" diameter Cicolac® yellow plastic
- Flow Control:** Internal 20 gpm regulator
- Frost Proof Valve:** 1 1/2" NPT female brass
- Standard Bury Depth:** 42"
- Activator:** Push handle
- Stanchion:** 1 1/4" IPS galvanized steel
- Waste:** 1 1/4" NPT female
- Performance:** 20 gpm @ 20 psi (flowing)
- Finish:** DuraJade™ powder coated finish


EYE/FACE WASH: SE-400

- Bowl:** 300 series stainless steel
- Spray Heads:** (6) brass, chrome-plated aerators, plastic covered brass bodies
- Frost Proof Valve:** 1 " NPT female brass
- Standard Bury Depth:** 42"
- Activator:** Push handle
- Shrouds:** Yellow polypropylene
- Performance:** 9.3 gpm @ 30 psi
- Compliance:** ANSI Z358.1
- Universal Emergency Sign Included**

NOTE: The maximum "static" pressure allowable for this unit is 80psi

OPTIONS

- 30GPM 30gpm regulator
- FLW2 Flow switches (2 Required)
- SSH Stainless steel showerhead
- BH Chrome plated brass showerhead



Job Name _____	
Location _____	
Architect/Engineer _____	
Sales Representative _____	
Wholesaler _____	
Date _____	Model # _____