

# Fine Fissured

PERFORMANCE SERIES MINERAL FIBER CEILING



## Specification Sheet

### Features & Benefits:

- 100% non-directional fissure pattern.
- Variety of edge detail options and panel sizes.
- High humidity and sag resistant.
- Available in 5 colors.
- No added formaldehyde.

See reverse for additional product specifications.


### Applications:

- Hospitality
- Retail
- Offices
- Education
- Healthcare
- Restaurants


### Attributes:

ITEM NUMBER	NOMINAL SIZE (Inches)	EDGE DETAIL	UL CLASSIFIED		LR	RECYCLED CONTENT %
			NRC	CAC		
<b>SAFETONE® CLASS A</b>						
HHF-150	24 x 24 x 5/8	Narrow Reveal	0.60	33	0.84	36-45
HHF-154	24 x 24 x 5/8	Reveal	0.60	33	0.84	36-45
HHF-157	24 x 24 x 5/8	Trim	0.60	33	0.84	36-45
HHF-194	24 x 48 x 5/8	Reveal	0.60	35	0.84	36-45
HHF-197	24 x 48 x 5/8	Trim	0.60	35	0.84	36-45
<b>PROTECTONE® (For specific UL fire resistant time-rated assemblies)</b>						
PFF-154	24 x 24 x 5/8	Reveal	0.55	35	0.84	47
PFF-157	24 x 24 x 5/8	Trim	0.55	35	0.84	47
PFF-197	24 x 48 x 5/8	Trim	0.55	40	0.84	47


ASTM E 1264 Classification: Type III, Form 2, Pattern C D




### Edge Details:




**TRIM EDGE**  
(Square) 15/16" Grid



**REVEAL EDGE**  
(Beveled) 15/16" Grid



**NARROW REVEAL EDGE**  
(Corner Bevel) 3/16" Grid



**NARROW REVEAL EDGE**  
(Corner Bevel)  
3/16" Grid (Bolt Slot)



**BioShield™**  
BioShield™ treatment included for added mold and mildew resistance.



# Product Specification Details

## Acoustical Ceilings

### 09 51 00

#### PART 2: PRODUCTS

##### 2.1 GENERAL

Provide Acoustical Ceiling Material manufactured to meet requirements of this specification in accordance with ASTM E 1264.

##### 2.2 MATERIALS

Acoustical Ceiling Units:

1. Type III
2. Form 2
3. Pattern [C] [D]
4. Discreet non-directional fissured lay-in panels and tile.
5. Size 5/8" thick x [24" x 24"] [24" x 48"]
6. Edge Detail [Trim (Square)] [Reveal] [Narrow Reveal]
7. Noise Reduction Coefficient (NRC) [0.55] [0.60]
8. Ceiling Attenuation Class (CAC) [33] [35] [40]
9. Light Reflectance Coefficient (LR) 0.84
10. Recycled Content [36-45] [47]
11. Color [White] [Beige Breeze] [Blondewood] [Silver Lining] [Wet Clay] [White Wash]
12. Flame Spread Classification (ASTM E 84, CAN/ULC-S102M) Class A
13. Underwriters Laboratories Inc. Fire-Resistance (ASTM E 119, CAN/ULC-S101M) Time-Rated Assembly\* [D203] [D205] [G208] [G218] [G248] [G255] [L201] [P204] [P259] [P260] [P261] [P262] [P264]
14. Manufacturer, subject to compliance with requirements of this specification, CertainTeed Ceilings
15. Product Name [Fine Fissured] [Protectone® Fine Fissured]

\* Relevant to Protectone® only. Refer to UL Fire Resistant Directory for specific design information.

---

Distributed by:

---

Characteristics, properties or performance of materials or systems manufactured by CertainTeed herein described are derived from data obtained under controlled test conditions. CertainTeed makes no warranties, express or implied, as to their characteristics, properties or performance under any variations from such conditions in actual construction. CertainTeed assumes no responsibility for the effects of structural movement.

NOTICE: The information in this document is subject to change without notice. CertainTeed assumes no responsibility for any errors that may inadvertently appear in this document.

---