

Department Shredder

40630 Dahle Professional Shredder



Known for its power and waste capacity, this Dahle Department Shredder provides a practical solution for accommodating the shredding needs of even the busiest offices. This machine can continually shred large quantities of paper for extended periods of time. Its attractive design and large waste bin make this a nice addition to any large office, copy room or communications center.

The Dahle 40630 has a 16" feed opening to easily accommodate letter, legal and wide computer paper. It has a maximum sheet capacity of 11/13 sheets at a time and features a large capacity waste bin capable of holding 45 gallons of shredded material.


Energy conservation continues to be a top priority at Dahle. Each shredder comes equipped with the revolutionary SmartPower Energy Management System. This multi-stage system reduces power consumption after ten minutes of sitting idle (sleep mode), and completely powers down after an additional 20 minutes

of inactivity. Dahle SmartPower will appeal to those interested in conserving energy as well as reducing electrical costs.

In order to provide slip free power to the cutting cylinders, a steel chain and gears connect the two components and provide maximum shredding capacity.

Just like any fine tuned machine, your shredder needs to be properly oiled to run at peak performance. This shredder is equipped with the Dahle EvenFlow Lubricator. This automatic oiler provides slow, continuous lubrication across the entire cutting mechanism and ensures peak performance.

Dahle's shredders are German Engineered using the latest technology and finest materials. The end result is a quality machine and peace of mind in knowing your Dahle shredder will provide many years of trouble free operation.



Features

- Feed Opening: 16"
- Sheet Capacity: 11/13
- Shred Size: 1/32" x 7/16"
- Security Level: P-6
- SmartPower Management
- EvenFlow Lubricator



Built in EvenFlow Lubrication System evenly lubricates the cutting cylinders reducing the risk of a paper jam.



The easy-to-use command dial controls all of the shredder's functions such as power up, reverse, and continuous run.



In order to provide slip free power to the cutting cylinders, a steel chain & gears connect the two for maximum capacity.

Specifications

Model	Feed Width	Capacity #20 / #16	Security Level	Shred Size	Waste Volume	Speed	Decibel Level	Features/Capabilities					Dimensions	Weight		
								Staples/Clips	CDs / DVDs	SmartPower	CleanTEC®	Safe Tech	ESP	Auto Oiler		
40630	16"	11 / 13	P-6	1/32" x 7/16"	45 gal	26 f/m	50 dB			●				●	38" x 29" x 20"	198 lbs

All performance data has been established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.



Dahle North America, Inc.
49 Vose Farm Road
Peterborough, NH 03458
(800) 995.1379 / www.dahle.com



Authorized Dealer