

Operating Instructions and Parts Manual

ATTENTION: TO INSURE SAFE AND EASY USE OF YOUR WESCO DRUM TRUCK, READ THESE INSTRUCTIONS BEFORE USING.

Description

The Wesco Drum Truck is designed specifically for lifting 30, 55 and 85 gallon drums. It is able to handle all poly and fiber drums, except overpacks. This heavy duty truck features a strap and floating axle reducing the effort required to break over with a balanced load.

This product is distributed by:

Wesco Industrial Products, Inc
1250 Welsh Road
North Wales, PA 19454
Tel: 215-699-7031 Fax: 215-699-3836

Contact the factory for parts information and ordering.
Visit us on the web at www.wescomfg.com

Unpacking

When unpacking the Wesco Product, check carefully for shipping damage and missing parts. If damage has occurred or any parts are missing, file a claim with the delivering carrier within 24 hours and notify the dealer from whom the unit was purchased.

Warranty Repairs

If the unit does not work properly, contact your dealer or the factory (215-699-7031) for units less than 90 days old.

Non-Warranty Service

If units are older than 90 days, repairs can be made easily on site with factory supplied parts.

NOTE: Do not send units to the factory for service without first obtaining a "Return Merchandise Authorization" (RMA) number from the customer service department. We will not be responsible for merchandise returned without proper authorization.

Warning

- DO NOT move with drum unless truck's nose prongs are positioned evenly and fully under drum.
- Use on level surfaces only
- DO NOT use on stairs or inclines.
- Periodically check for loose or worn hardware; If found replace at once.

Spare Parts

Item	Part No.	Description	Qty.
1	150596	10" Wheel	2
2	108208	1" Flat Washer	4
3	108218	Cotter Pin (3/16 x 1 1/2)	2
4	150303	Strap (Handle & Assembly)	1
5	108900	1/4" Hex Screw	2
6	108929	1/4" Lock Nut	2
7	051346	Upper Spring Housing	1
8	051347	Floating Axle Assembly	1
9	051356	Axle Hardware Set	1
10	108433	Handgrip	2
11	050187	Nose Pad Set	1

General Safety Information

Warning: The Wesco Drum Trucks are intended for specific functions. Please adhere to the following instructions to insure safe and proper use.

- (1) Maximum capacity - 1000 Lbs.
- (2) Do not exceed rated capacity. Injury to persons or property may result from overloading and misuse.
- (3) **Do Not use on Overpack Drums**

Operating Instructions

- (1) Position nose pads of truck in contact with the bottom edge of the drum
- (2) Wrap belt around the drum and place it in the fork grooves
 - a. Make sure the belt is placed around the larger diameter, upper section of the drum
 - b. Make sure the belt is not twisted
- (3) Tighten belt so that the truck frame touches the upper part of the drum
- (4) Pull truck back carefully, until drum rests on the nose pads securely then retighten the belt
- (5) Upon unloading, be sure to hold the truck securely when loosening the belt

LIMITED WARRANTY

WESCO INDUSTRIAL PRODUCTS (WESCO) warrants to the purchaser of this product for a period of ninety (90) days from the date of purchase that this product shall be free of defects in material and/or workmanship, as follows:

1. WESCO will supply, at no charge, new or rebuilt replacements for any part that fails through a defect in material and/or workmanship during the warranty period. To obtain warranty service, you must deliver the product prepaid, to the WESCO factory.

2. This warranty does not cover any product or product part which has been subject to accident, misuse, abuse or negligence. WESCO shall only be liable under this warranty if the product is used the manner intended by the manufacturer as specified in the written instructions furnished with this product.

REPAIR OR REPLACEMENT AS PROVIDED UNDER THIS WARRANTY IS THE EXCLUSIVE REMEDY OF THE PURCHASER. ANY EXPRESS WARRANTY NOT PROVIDED IN THIS WARRANTY DOCUMENT, AND ANY REMEDY FOR BREACH OF CONTRACT THAT, BUT FOR THIS PROVISION, MIGHT ARISE BY IMPLICATION OR OPERATION OF LAW, IS HEREBY EXCLUDED AND DISCLAIMED. UNDER NO CIRCUMSTANCES SHALL WESCO BE LIABLE TO PURCHASER OR ANY OTHER PERSON FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES, WHETHER ARISING OUT OF BREACH OF WARRANTY, EXPRESS OR IMPLIED, A BREACH OF CONTRACT OR OTHERWISE. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ANY IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR ANY PARTICULAR PURPOSE ARE EXPRESSLY LIMITED IN DURATION TO THE DURATION OF THIS LIMITED WARRANTY.

Some states do not allow the exclusion or limitation of incidental or consequential damages, or allow limitations on how long any implied warranty lasts, so the above limitations may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.