



Lift Tables

LIFT & TILT SCISSOR LIFT TABLE



Lift & Tilt Scissor Lift Tables automatically tilts to 45 degrees at full elevation when platform is raised, providing optimum positioning of the load.

L"	W"	Capacity	Model
29 ¹ / ₂ "	19 ¹ / ₂ "	400 lb.	168079
36"	24"	600 lb.	168080

MOBILE SCISSOR LIFT TABLE

Mobile Scissor Lift Tables have a foot operated hydraulic lift pump for smooth lifting and positive height adjustment without a downward drift. The ergonomic design reduces risk of injury from lifting and bending. Some models feature a hook-on bin to carry parts.



L"	W"	Capacity	Type	Model
27 ¹ / ₃ "	17 ¹ / ₂ "	330 lb.	Single Scissor	168073
32"	19"	550 lb.	Single Scissor	168074
39 ¹ / ₃ "	20 ¹ / ₄ "	1100 lb.	Single Scissor	168075
39 ¹ / ₃ "	20 ¹ / ₄ "	1650 lb.	Single Scissor	168076
39 ¹ / ₃ "	20 ¹ / ₄ "	660 lb.	Double Scissor	168077
39 ¹ / ₃ "	20 ¹ / ₄ "	1100 lb.	Double Scissor	168078
29 ¹ / ₂ "	19 ³ / ₄ "	660 lb.	Single Scissor W/Hook on Bin	954850
35 ¹ / ₂ "	23 ¹ / ₂ "	1100 lb.	Single Scissor W/Hook on Bin	954852
40"	20"	2200 lb.	Single Scissor	988933

WORK POSITIONING POST LIFT TABLE

Work Positioning Post Lift Tables are foot operated and can be used at conveyor or production lines, as an adjustable workbench or positioning table, or at the dock loading and unloading trucks.



L"	W"	Capacity	Model
18"	18"	500 lb.	232054
18"	36"	1000 lb.	232056
24"	36"	6000 lb.	232066
32"	48"	6000 lb.	232068
24"	36"	2000 lb.	241381
32"	48"	2000 lb.	241382
16"	16"	2000 lb.	501098