

C70RX CAT® AUTO RIDE-ON SWEEPER, 70" CLEANING PATH

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Wide cleaning path offers easy maneuverability.
- Durable plastic and metal body protects against corrosion and impact.
- Front water misters provide dust suppression.
- Large 42.2 gallon capacity hopper and 60.7 gallon capacity solution tank reduce refill times and increase productivity.
- Shake vibration technology shakes dust off of the filters to improve suction power.
- Bright LED headlight, blue pedestrian warning light, amber warning light, seatbelt, and diamond tread platform provide additional safety.
- (8) 6V 305Ah batteries help extend run time.
- USB charger, phone pocket, and cup holder add convenience.

Includes: (6) filters, (1) underneath main roller brush, (2) side brushes, (2) sets of keys, (4) batteries, and (1) charger.

SPECIFICATIONS:

Global Part Number:	641820, 641821
Cleaning Path:	74.8"
Battery Run Time:	5-6 hours
Clean Cap. Sq. Ft./Hr.:	204,514
Horsepower:	8.4 HP
Speed MPH:	10 MPH
Brush Motor RPM:	100RPM (Side) / 535RPM (Roller)
Wattage:	6161 W
Decibels:	< 76dB
Weight Capacity:	1323 lbs.
Turning Radius:	74"
Capacity (Gallons):	42.2 (Hopper) / 60.7 (Solution)
Battery Type:	8 x 6V 305Ah
Dimensions (WxDxH):	75" x 91" x 95"
Product Weight:	2756 lbs.
Vacuum Motor	48V/218W x 2 Vacuum Motors
Drive Motor	48V/2,200W
Construction:	PE Plastic & Powder Coated Steel
Certifications:	ETL, cETL for Battery Charger



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C49R CAT® AUTO RIDE-ON SWEEPER, 49" CLEANING PATH

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Wide cleaning path offers easy maneuverability.
- Durable plastic and metal body protects against corrosion and impacts.
- Front water misters provide dust suppression.
- Large 26.4 gallon capacity hopper and 7.9 gallon capacity water tank reduce refill times and increase productivity.
- Shake vibration technology shakes dust off of the filters to improve suction power.
- Bright LED headlight, blue pedestrian warning light, amber warning light, seatbelt, and diamond tread platform provide additional safety.
- (4) 6V 200Ah batteries help extend run time.
- USB charger, phone pocket, and cup holder add convenience.

Includes: (6) filters, (1) underneath main roller brush, (2) side brushes, (2) sets of keys, (4) batteries, and (1) charger.

SPECIFICATIONS:

Global Part Number:	641748
Cleaning Path:	49"
Battery Run Time:	5 Hours
Clean Cap. Sq. Ft./Hr.:	78,740
Horsepower:	2
Speed MPH:	4
Brush Motor RPM:	1700
Wattage:	1500
Decibels:	71
Weight Capacity:	660 lbs.
Turning Radius:	78"
Capacity (Gallons):	26.4 (Hopper) / 7.9 (Water Tank)
Battery Type:	4 x 6V 200AH
Dimensions (WxDxH):	40" x 55" x 47"
Product Weight:	919 lbs.
Vacuum Motor (V/W):	24/380
Drive Motor (V/W):	24/800
Construction:	PE Plastic & Powder Coated Steel
Certifications:	ETL, cETL for Battery Charger



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C40R CAT® AUTO RIDE-ON FLOOR SCRUBBER, 40" CLEANING PATH

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



Features a 7" LCD
touchscreen interface

FEATURES:

- Highly visible 7" LCD touchscreen interface keeps control at your fingertips.
- Wide cleaning path offers easy maneuverability.
- Rotationally molded polyethylene tanks provide corrosion- and impact-resistance.
- Digital controller and integral battery charger, powered by the Airvolt® battery management system technology, allow for optimal charging and longer run time.
- 55-187 lb. brush pressure with enhanced heavy-duty motor boosts cleaning efficiency.
- Large 40 gallon solution tank and 45 gallon recovery tank reduce refill time and increase productivity.
- Heavy-duty cast aluminum squeegee assembly and rear mounted squeegee hooks allow for easy storage.
- Bright LED headlight, blue pedestrian warning light, amber warning light, seatbelt, front bumper, and diamond tread platform provide additional safety.
- USB charger, phone pocket, and cup holder add convenience.

Includes: (3) 12V batteries, set of squeegee blades, and pad driver.

Scrub brush and floor pads sold separately.

SPECIFICATIONS:

Global Part Number:	641747
Cleaning Path:	40"
Brush Motor RPM:	220
Clean Cap. Sq. Ft./Hr.:	73,490
Brush Motor HP:	0.75 x 2
Pad Pressure:	55-187 lbs.
Speed MPH:	4.04
Wattage:	550 x 2 (Brush) / 738 (Vacuum Motor)
Decibels:	70
Squeegee Width:	47.25"
Water Lift:	74"
Tank Capacity (Gallons):	40 (Solution) / 45 (Recovery)
Battery:	3 x 190 Ah
Dimensions (WxDxH):	65.7" x 40.2" x 51.6"
Product Weight:	1,056 lbs.
Vacuum Motor HP:	1
Turning Radius:	34"
Construction:	PE Plastic
Run Time (Per Charge):	4.5 Hours
Certifications:	ETL, cETL (For Charger)



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C26R CAT® AUTO RIDE-ON FLOOR SCRUBBER, 26" CLEANING PATH

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Wide cleaning path offers easy maneuverability."
- Rotationally molded polyethylene tanks provide corrosion and impact resistance.
- Improved 110lb brush pressure and half horsepower brush motor boosts cleaning efficiency
- Includes front bumper to increase safety and unit lifespan
- Improved vacuum picks up heavier debris and produces a deeper clean
- Large 23 gallon solution tank and 26 gallon recovery tank reduce refill time and increase productivity.
- Heavy-duty cast aluminum squeegee assembly and rear mounted squeegee hooks allow for easy storage.
- Bright LED headlight, blue pedestrian warning light, seatbelt, front bumper, and diamond tread platform provide additional safety.
- USB charger, phone pocket, and cup holder add convenience.

Scrub brush and floor pads sold separately.

SPECIFICATIONS:

Global Part Number	641811
Cleaning Path	27 1/2"
Squeegee Width	33 3/4"
Brush Motor Voltage	24V
Brush Motor HP	2 x 1/2 HP
Brush RPM	180 RPM
Brush Pad Pressure	110 lbs
Forward Speed	0 - 3.11 MPH
Drive Motor Voltage / HP	24V / 1/3HP
Cleaning Capacity	37,600 sq. ft/hr
Solution Tank Capacity	23.7 gallons
Recovery Tank Capacity	26.4 gallons
Battery	2 x 120 Ah
Dimensions (WxDxH)	54.9" x 29.5" x 46.9"
Product Weight	325 lbs.
Vacuum Motor HP	2/3 HP
Max Gradient	12%
Construction	PE Plastic
Run Time (Per Charge)	4.5 hours
Certifications	ETL, cETL (For charger)



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C20E CAT® ELECTRIC WALK-BEHIND CORDED AUTO FLOOR SCRUBBER, 20" CLEANING PATH

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Wide cleaning path offers easy maneuverability.
- Rotationally molded polyethylene tanks provide corrosion- and impact-resistance.
- Pad Assist feature helps pull the machine forward for ease of use.
- 110 lb. brush pressure with enhanced heavy-duty motor boosts cleaning efficiency.
- Large 12 gallon solution tank and 15 gallon recovery tank reduce refill times and increase productivity.
- Heavy-duty 30"W cast aluminum squeegee assembly helps remove cleaning solution.
- Built-in phone pocket and cup holder add convenience.

Includes: 82'L safety yellow power cord with GFCI plug, set of squeegee blades, and pad driver.

Scrub brush (model 262003) and floor pads sold separately.

SPECIFICATIONS:

Global Part Number:	641745
Cleaning Path:	20"
Motor Amps:	9.2
Clean Cap. Sq. Ft./Hr.:	18,800
Horsepower:	1.02
Pad Pressure:	99 lbs.
Global Part Brush Motor RPM:	180
Wattage/Voltage:	375 (Brush)/1200 (Vacuum)
Decibels:	68
Squeegee Width:	30"
Water Lift:	92"
Tank Capacity (Gallons):	12 (Solution) / 15 (Recovery)
Power Cord Length:	82'
Dimensions (WxDxH):	22" x 46" x 38"
Product Weight:	253 lbs.
Vacuum Motor HP:	1.6
Brush Motor HP:	1.02
Construction:	PE Plastic
Certifications:	ETL, cETL



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C20T CAT® AUTO FLOOR SCRUBBER WITH TRACTION DRIVE, 20" CLEANING PATH

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



Features a 7" LCD
touchscreen interface

FEATURES:

- Highly visible 7" LCD touchscreen interface keeps control at your fingertips.
- Wide cleaning path offers easy maneuverability.
- Rotationally molded polyethylene tanks provide corrosion- and impact-resistance.
- Multiple drive settings allow flexibility, including: variable speed control transaxle drive and forward and reverse drive.
- 100 lb. pad pressure with enhanced heavy-duty motor boosts cleaning efficiency.
- Digital controller and integral battery charger, powered by the Airvolt® battery management system technology, allow for optimal charging and longer run time.
- Large 15 gallon solution tank and 17 gallon recovery tank reduce refill times and increase productivity.
- Heavy-duty 30"W cast aluminum squeegee assembly helps remove cleaning solution.
- Built-in phone pocket and cup holder add convenience.

Includes: (2) 12V batteries, set of squeegee blades, and pad driver.

Scrub brush (model 262003) and floor pads sold separately.

SPECIFICATIONS:

Global Part Number:	641746
Cleaning Path:	20"
Brush Motor RPM:	220
Clean Cap. Sq. Ft./Hr.:	24,218
Brush Motor HP:	3/4
Pad Pressure:	100 lbs.
Speed MPH:	2.2
Wattage:	550 (Brush) / 390 (Vacuum Motor)
Decibels:	68
Squeegee Width:	30"
Water Lift:	46"
Tank Capacity (Gallons):	15 (Solution) / 17 (Recovery)
Battery:	2 x 120 Ah'
Dimensions (WxDxH):	21.7" x 51.2" x 40.6"
Product Weight:	407.5 lbs.
Vacuum Motor HP:	0.5
Turning Radius:	26"
Construction:	PE Plastic
Run Time (Per Charge):	4.5 Hours
Certifications:	ETL, cETL (For Charger)



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C21V CAT® STAINLESS STEEL HEPA WET/DRY VACUUM, 21 GALLON CAPACITY

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Stainless steel construction provides long-lasting strength and durability.
- HEPA cartridge filter and reusable filter bag capture and eliminate fine dust.
- Large 21 gallon tank capacity increases productivity.
- On-board tool storage and 33' GFCI power cord boost cleaning efficiency.
- Dolly design with large push handle enhances maneuverability.
- Removable canister allows for easy maintenance.
- Dissipative ground chain helps protect against static electricity.
- Two large rear wheels with two front casters offer easy mobility.

Includes: (1) 8.2' long hose, (2) extension wands, (1) dry floor nozzle, (1) squeegee nozzle, (1) round brush, (1) metal crevice nozzle, (1) filter bag, and (1) HEPA filter cartridge.

SPECIFICATIONS:

Global Part Number:	641757
Voltage:	120
CFM:	120
Construction:	Stainless Steel/Plastic
Water Lift:	70"
Wattage:	1400
Cleaning Width:	14"
Amps:	12
Hertz:	60
Hose Length:	8.2'
Type:	Wet/Dry
Tank Capacity (Gallons):	21
Power Cord Length:	50'
Dimensions (WxDxH):	24" x 18" x 40"
Product Weight:	50.7 lbs.
Filter Type:	HEPA Cartridge & Cloth Filter Bag
Color Finish:	Black/Yellow
Hose Diameter:	1-1/2"
Certifications:	ETL, cETL



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C16V CAT® STAINLESS STEEL HEPA WET/DRY VACUUM, 16 GALLON CAPACITY

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Stainless steel construction provides long-lasting strength and durability.
- HEPA cartridge filter and disposable filter bags capture and eliminate fine dust.
- Large 16 gallon tank capacity increases productivity.
- On-board tool storage and 15' GFCI power cord boost cleaning efficiency.
- Dolly design with large foam grip push handle enhances maneuverability.
- Two large rear wheels with two front casters offer easy mobility.

Includes: (1) 13' long hose, (2) extension wands, (1) 14" wet/dry floor brush, (1) round brush, (1) crevice nozzle, (1) paper filter bag, and (1) HEPA filter cartridge.

SPECIFICATIONS:

Global Part Number:	641759
Voltage:	120
CFM:	115
Construction:	Stainless Steel/Plastic
Water Lift:	115.5"
Wattage:	1200
Cleaning Width:	14"
Amps:	10
Hertz:	60
Decibels:	80
Peak Horsepower:	3.5
Tank Capacity (Gallons):	16
Power Cord Length:	15'
Dimensions (WxDxH):	21" x 22" x 37"
Product Weight:	52 lbs.
Filter Type:	HEPA Cartridge & Paper Filter Bag
Color Finish:	Black/Yellow
Hose Diameter:	1-1/2"
Certifications:	ETL, cETL



For more information, visit globalindustrial.com
or call 1-800-645-1232.



C06V CAT® STAINLESS STEEL HEPA WET/DRY VACUUM, 6.6 GALLON CAPACITY

AVAILABLE EXCLUSIVELY FROM GLOBAL INDUSTRIAL™



FEATURES:

- Stainless steel construction offers long-lasting strength and durability.
- HEPA cartridge filter and disposable filter bags capture and eliminate fine dust.
- On-board tool storage and 15' GFCI power cord boost cleaning efficiency.
- Four swivel casters provide easy mobility.

Includes: (1) 8-1/2' long hose, (2) extension wands, (1) 12" wet/dry floor brush, (1) round brush, (1) crevice nozzle, (1) paper filter bag, and (1) HEPA filter cartridge.

SPECIFICATIONS:

Global Part Number:	641758
Voltage:	120
CFM:	115
Construction:	Stainless Steel/Plastic
Water Lift:	78"
Wattage:	1200
Cleaning Width:	12"
Amps:	10
Hertz:	60
Decibels:	79
Peak Horsepower:	3.5
Tank Capacity (Gallons):	6.6
Power Cord Length:	15'
Dimensions (WxDxH):	14" x 14" x 21"
Product Weight:	16.4 lbs.
Filter Type:	HEPA & Paper Filter Bag
Color Finish:	Black/Yellow
Hose Diameter:	1-1/4"
Certifications:	ETL, cETL



For more information, visit globalindustrial.com
or call 1-800-645-1232.

