

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, LCP, L7XP, L7XPR, L7XF and L7XFR.

CONSTRUCTION

Aluminum white sphere.

Polyester powder coat paint.

25 degree vertical tilt standard.

Antique bronze, oil-rubbed bronze, brushed nickel and white finishes are one piece aluminum reflector with integral flange.

INSTALLATION

Socket-to-trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.


LISTING

U.L. Listed to U.S. and Canadian safety standards.


Damp location listed.

6" Full Reflector Trim

7E1



STANDARD EYEBALL
Wide Flange



Specifications

Height: 4 (10.2)

Lamp opening: 4-7/8 (12.4)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise specified.

ORDERING INFORMATION

All configurations of this product are considered "standard" and have short lead times.

Example: 7E1 TOR

7E1	
Series	Finish
7E1	(blank) White eyeball BN Brushed nickel ORB Oil-rubbed bronze BZA Antique bronze

TOR
Mounting method
TOR Torsion springs

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6, L7XP, L7XF
		65 BR30	L7X, L7XR, LC6, L7XP, L7XF
	Fluorescent	18 TRT	L7XF, L7XFR

7E1 6" Standard Eyeball Full Reflector Trim
