

# Electric Auto Floor Scrubber

## Model # 261990

TECHNICAL SPECIFICATION	
Clean width	20"
Squeegee width	30"
Work capacity	1880 sq.ft/hr
Pad Pressure	84 lbs
Brush RPM	180
Brush motor	120V/750W/6.25Amp/60HZ
Suction motor	120V/1200W/10Amp/60HZ
Solution tank	12 gallon
Recovery tank	15 gallon
Machine dimensions (Excluding squeegee)	46" x 22" x 38" (L x W x H)
Cord	12 AWG Cord, 82 ft
Machine weight	209 lb



### **AUTOMATIC ELECTRIC FLOOR SCRUBBER**

Automatic Floor Scrubber Machine Offers Durable Construction And Is Easy To Use.

Rotationally molded polyethylene tanks are corrosion and impact resistant. 20" cleaning pad provides a wide 20" cleaning path for greater coverage in less time. Pad Assist feature helps pull the machine forward by the friction of the scrub deck pad against the floor, the operator simply needs to tilt the scrubber forward to enable spinning pad to contact the floor. The Floor scrubber is powered by a 1.6HP motor that offers 113" water lift, 180 RPM and a coverage rate of 18,800 sq. Ft. per hour.

The scrubber features a 12 gallon solution tank and a 15 gallon recovery tank. The scrubber has a heavy duty 30"W cast aluminum squeegee assembly for removing cleaning solution. Floor cleaning machine includes 82'L safety yellow power cord with GFCI plug. Set of squeegee blades and pad driver are included. Scrub brush and floor pads sold separately. 120V. ETL and cETL listed. Three year limited warranty; lifetime warranty on housing.