

COMMERCIAL FAN-FORCED WALL HEATERS

VFK SERIES



APPLICATIONS:

Attics
Basements
Entryways
Large Rooms
Offices
Remodels

CONTEMPORARY DESIGN

- Commercial grade steel grille designed to provide a sleek appearance and rugged use

UNIFORM DISTRIBUTION OF WARMTH

- Built-in fan delay switch energizes fan motor only after elements are heated, which prevents discharge of unheated air
- Integral double pole thermostat allows for easy adjustment of room temperature to maintain desired comfort level and a positive OFF to assure heater will not operate if not needed

SAFETY STANDARDS COMPLIANT


- Safety listed by Intertek (ETL) for use in the USA and Canada complying with ANSI/UL2021 and C22.2, NO. 56 Safety Standards
- Manual-reset thermal overheat protector disconnects power in the event of overheating due to accidental blockage

DURABILITY AND EASY MAINTENANCE

- All units have a permanently lubricated, totally enclosed fan motor, which creates long life and low maintenance, and gently distributes warmth throughout the area

Catalog Number	Voltage	Wattage	Phase	AMPS
VFK151F	120	1500	1	12.5
VFK204F	240/208	2000/1500	1	8.3/7.2
VFK303F	347	3000	1	8.6
VFK304F	240	3000	1	12.5
VFK306F	600	3000	3	5
VFK403F	347	4000	1	11.5
VFK404F	240/208	4000/3000	1	16.7/14.4
VFK406F	600	4000	3	6.7
VFK408F	208	4000	1	19.2
VFK483F	347	4800	1	13.8
VFK484F	240/208	4800/3600	1	20/17.3
VFK486F	600	4800	3	8
VFK4083F	208	4000	3	11.1
VFK487F	277/240	4800/3600	1	17.3/15
VFK488F	208	4800	1	23.1
VFK4883F	208	4800	3	13.3
Accessories				
VFKSM	Surface mounting frame for surface installations. 3-13/16" deep			
VFKS1	1" deep surface mounting frame for semi-recessed installation			
VFKS2	2" deep surface mounting frame for semi-recessed installation			
VFKSFC	14 gauge security front cover			

DIMENSIONS



MOUNTING LIMITATIONS

Do not install heater closer than 8" from floor or adjacent wall surface, behind towel rack or door, upside down or side up, in floor, ceiling or closet.

