



## Safety Data Sheet

Copyright, 2014, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document Group:</b>	31-8643-4	<b>Version Number:</b>	1.02
<b>Issue Date:</b>	04/14/14	<b>Supersedes Date:</b>	08/23/13

### SECTION 1: Identification

#### 1.1. Product identifier

3M™ Scotch-Brite™ Products, EXL PRO Deburring Wheels 9S FIN, 10S FIN, 11S FIN

#### 1.2. Recommended use and restrictions on use

##### Recommended use

Abrasive Product

#### 1.3. Supplier's details

<b>MANUFACTURER:</b>	3M
<b>DIVISION:</b>	Abrasive Systems Division
<b>ADDRESS:</b>	3M Center, St. Paul, MN 55144-1000, USA
<b>Telephone:</b>	1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

### SECTION 2: Hazard identification

#### 2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

#### 2.2. Label elements

##### Signal word

Not applicable.

##### Symbols

Not applicable.

##### Pictograms

Not applicable.

#### 2.3. Hazards not otherwise classified

None.

37% of the mixture consists of ingredients of unknown acute oral toxicity.

### SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Silicon Carbide Mineral	409-21-2	35 - 45
Inorganic Fluoride	14075-53-7	1 - 10
Lubricant	8002-74-2	1 - 5
Quartz Silica	14808-60-7	0.01 - 0.2
Carbon Black	1333-86-4	0.02 - 0.2
Titanium Dioxide	13463-67-7	0 - 0.2
Cured Resin	Mixture	25 - 40
Nylon Fiber	Mixture	10 - 20

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

**Inhalation:**

Remove person to fresh air. If you feel unwell, get medical attention.

**Skin Contact:**

Wash with soap and water. If signs/symptoms develop, get medical attention.

**Eye Contact:**

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

**If Swallowed:**

No need for first aid is anticipated.

#### 4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

#### 4.3. Indication of any immediate medical attention and special treatment required

Not applicable

### SECTION 5: Fire-fighting measures

#### 5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

#### 5.2. Special hazards arising from the substance or mixture

None inherent in this product.

#### Hazardous Decomposition or By-Products

Substance

Carbon monoxide  
Carbon dioxide

Condition

During Combustion  
During Combustion

#### 5.3. Special protective actions for fire-fighters

No unusual fire or explosion hazards are anticipated.

### SECTION 6: Accidental release measures

**6.1. Personal precautions, protective equipment and emergency procedures**

Observe precautions from other sections.

**6.2. Environmental precautions**

Not applicable.

**6.3. Methods and material for containment and cleaning up**

Not applicable.

**SECTION 7: Handling and storage**

**7.1. Precautions for safe handling**

For industrial or professional use only. Avoid breathing of dust created by sanding, grinding or machining. Damaged product can break apart during use and cause serious injury to face or eyes. Check product for damage such as cracks or nicks prior to use. Replace if damaged. Always wear eye and face protection when working at sanding or grinding operations or when near such operations. Combustible dust may form by action of this product on another material (substrate). Dust generated from the substrate during use of this product may be explosive if in sufficient concentration with an ignition source. Dust deposits should not be allowed to accumulate on surfaces because of the potential for secondary explosions.

**7.2. Conditions for safe storage including any incompatibilities**

No special storage requirements.

**SECTION 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Occupational exposure limits**

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Carbon Black	1333-86-4	Amer Conf of Gov. Indust. Hyg.	TWA(inhalable fraction):3 mg/m3	
Carbon Black	1333-86-4	Chemical Manufacturer Rec Guid	TWA:0.5 mg/m3	
Carbon Black	1333-86-4	US Dept of Labor - OSHA	TWA:3.5 mg/m3	
Titanium Dioxide	13463-67-7	Amer Conf of Gov. Indust. Hyg.	TWA:10 mg/m3	
Titanium Dioxide	13463-67-7	Chemical Manufacturer Rec Guid	TWA(as respirable dust):5 mg/m3	
Titanium Dioxide	13463-67-7	US Dept of Labor - OSHA	TWA(as total dust):15 mg/m3	
Quartz Silica	14808-60-7	Amer Conf of Gov. Indust. Hyg.	TWA(respirable fraction):0.025 mg/m3	
Quartz Silica	14808-60-7	US Dept of Labor - OSHA	TWA concentration(as total dust):0.3 mg/m3;TWA concentration(respirable):0.1 mg/m3(2.4 millions of particles/cu. ft.)	

Silicon Carbide Mineral	409-21-2	Amer Conf of Gov. Indust. Hyg.	TWA(as fiber):0.1 fiber/cc;TWA(inhalable fraction):10 mg/m3;TWA(respirable fraction):3 mg/m3	
Silicon Carbide Mineral	409-21-2	US Dept of Labor - OSHA	TWA(as total dust):15 mg/m3;TWA(respirable fraction):5 mg/m3	
Lubricant	8002-74-2	Amer Conf of Gov. Indust. Hyg.	TWA(as fume):2 mg/m3	

Amer Conf of Gov. Indust. Hyg. : American Conference of Governmental Industrial Hygienists  
 American Indust. Hygiene Assoc : American Industrial Hygiene Association  
 Chemical Manufacturer Rec Guid : Chemical Manufacturer's Recommended Guidelines  
 US Dept of Labor - OSHA : United States Department of Labor - Occupational Safety and Health Administration  
 TWA: Time-Weighted-Average  
 STEL: Short Term Exposure Limit  
 CEIL: Ceiling

**8.2. Exposure controls**

**8.2.1. Engineering controls**

Provide appropriate local exhaust ventilation for sanding, grinding or machining. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment. Provide local exhaust at process emission sources to control exposure near the source and to prevent the escape of dust into the work area. Ensure that dust-handling systems (such as exhaust ducts, dust collectors, vessels, and processing equipment) are designed in a manner to prevent the escape of dust into the work area (i.e., there is no leakage from the equipment).

**8.2.2. Personal protective equipment (PPE)**

**Eye/face protection**

To minimize the risk of injury to face and eyes, always wear eye and face protection when working at sanding or grinding operations or when near such operations. Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:  
 Safety Glasses with side shields

**Skin/hand protection**

Wear appropriate gloves to minimize risk of injury to skin from contact with dust or physical abrasion from grinding or sanding.

**Respiratory protection**

Assess exposure concentrations of all materials involved in the work process. Consider material being abraded when determining the appropriate respiratory protection. Select and use appropriate respirators to prevent inhalation overexposure. An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:  
 Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

**SECTION 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

<b>General Physical Form:</b>	Solid
<b>Odor, Color, Grade:</b>	Solid Abrasive Product
<b>Odor threshold</b>	<i>Not Applicable</i>
<b>pH</b>	<i>Not Applicable</i>
<b>Melting point</b>	<i>Not Applicable</i>
<b>Boiling Point</b>	<i>Not Applicable</i>
<b>Flash Point</b>	<i>Not Applicable</i>
<b>Evaporation rate</b>	<i>Not Applicable</i>
<b>Flammability (solid, gas)</b>	Not Classified
<b>Flammable Limits(LEL)</b>	<i>Not Applicable</i>
<b>Flammable Limits(UEL)</b>	<i>Not Applicable</i>
<b>Vapor Pressure</b>	<i>Not Applicable</i>
<b>Vapor Density</b>	<i>Not Applicable</i>
<b>Specific Gravity</b>	<i>Not Applicable</i>
<b>Solubility In Water</b>	<i>Not Applicable</i>
<b>Solubility- non-water</b>	<i>Not Applicable</i>
<b>Partition coefficient: n-octanol/ water</b>	<i>Not Applicable</i>
<b>Autoignition temperature</b>	<i>Not Applicable</i>
<b>Decomposition temperature</b>	<i>Not Applicable</i>
<b>Viscosity</b>	<i>Not Applicable</i>

**SECTION 10: Stability and reactivity**

**10.1. Reactivity**

This material is considered to be non reactive under normal use conditions.

**10.2. Chemical stability**

Stable.

**10.3. Possibility of hazardous reactions**

Hazardous polymerization will not occur.

**10.4. Conditions to avoid**

None known.

**10.5. Incompatible materials**

None known.

**10.6. Hazardous decomposition products**

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

## SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

### 11.1. Information on Toxicological effects

#### Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

#### Inhalation:

Dust from grinding, sanding or machining may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

#### Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

#### Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Dust created by grinding, sanding, or machining may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

#### Ingestion:

No health effects are expected.

#### Carcinogenicity:

Ingredient	C.A.S. No.	Class Description	Regulation
Carbon Black	1333-86-4	Grp. 2B: Possible human carc.	International Agency for Research on Cancer
Quartz Silica	14808-60-7	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer
SILICA, CRYST AIRRESP	14808-60-7	Known human carcinogen	National Toxicology Program Carcinogens
Titanium Dioxide	13463-67-7	Grp. 2B: Possible human carc.	International Agency for Research on Cancer

#### Additional Information:

This document covers only the 3M product. For complete assessment, when determining the degree of hazard, the material being abraded must also be considered.

This product contains titanium dioxide and quartz (crystalline) silica. Cancer of the lungs has been associated with inhalation of high levels of titanium dioxide in animal studies, and occupational exposure to inhaled quartz silica has been associated with silicosis and lung cancer. No exposure to titanium dioxide or quartz silica is expected during the normal handling and use of this product. Titanium dioxide and quartz silica were not detected when air sampling was conducted during simulated use of similar products containing these substances. Therefore, the health effects associated with titanium dioxide and quartz (crystalline) silica are not expected during the normal use of this product.

#### Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

#### Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
Silicon Carbide Mineral	Dermal	Rat	LD50 > 2,000 mg/kg

Silicon Carbide Mineral	Ingestion	Rat	LD50 > 2,000 mg/kg
Lubricant	Dermal	Rabbit	LD50 > 5,000 mg/kg
Lubricant	Ingestion	Rat	LD50 > 5,000 mg/kg
Quartz Silica	Dermal		LD50 estimated to be > 5,000 mg/kg
Quartz Silica	Ingestion		LD50 estimated to be > 5,000 mg/kg
Carbon Black	Dermal	Rabbit	LD50 > 3,000 mg/kg
Carbon Black	Ingestion	Rat	LD50 > 8,000 mg/kg
Titanium Dioxide	Dermal	Rabbit	LD50 > 10,000 mg/kg
Titanium Dioxide	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 6.82 mg/l
Titanium Dioxide	Ingestion	Rat	LD50 > 10,000 mg/kg

ATE = acute toxicity estimate

**Skin Corrosion/Irritation**

Name	Species	Value
Quartz Silica		No significant irritation
Carbon Black	Rabbit	No significant irritation
Titanium Dioxide	Rabbit	No significant irritation

**Serious Eye Damage/Irritation**

Name	Species	Value
Carbon Black	Rabbit	No significant irritation
Titanium Dioxide	Rabbit	No significant irritation

**Skin Sensitization**

Name	Species	Value
Titanium Dioxide	Human and animal	Not sensitizing

**Respiratory Sensitization**

Name	Species	Value

**Germ Cell Mutagenicity**

Name	Route	Value
Quartz Silica	In Vitro	Some positive data exist, but the data are not sufficient for classification
Quartz Silica	In vivo	Some positive data exist, but the data are not sufficient for classification
Carbon Black	In Vitro	Not mutagenic
Carbon Black	In vivo	Some positive data exist, but the data are not sufficient for classification
Titanium Dioxide	In Vitro	Not mutagenic
Titanium Dioxide	In vivo	Not mutagenic

**Carcinogenicity**

Name	Route	Species	Value
Quartz Silica	Inhalation	Human and animal	Carcinogenic
Carbon Black	Dermal	Mouse	Not carcinogenic
Carbon Black	Ingestion	Mouse	Not carcinogenic
Carbon Black	Inhalation	Rat	Carcinogenic
Titanium Dioxide	Ingestion	Multiple animal species	Not carcinogenic
Titanium Dioxide	Inhalation	Rat	Carcinogenic

**Reproductive Toxicity**

**Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test Result	Exposure Duration

**Target Organ(s)**

**Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration

**Specific Target Organ Toxicity - repeated exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Silicon Carbide Mineral	Inhalation	pneumoconiosis	Some positive data exist, but the data are not sufficient for classification		HHA	
Inorganic Fluoride	Inhalation	bone, teeth, nails, and/or hair	Some positive data exist, but the data are not sufficient for classification		HHA	
Quartz Silica	Inhalation	silicosis	Causes damage to organs through prolonged or repeated exposure	Human	NOAEL Not available	occupational exposure
Carbon Black	Inhalation	pneumoconiosis	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	occupational exposure
Titanium Dioxide	Inhalation	respiratory system	Some positive data exist, but the data are not sufficient for classification	Rat	LOAEL 0.010 mg/l	2 years
Titanium Dioxide	Inhalation	pulmonary fibrosis	All data are negative	Human	NOAEL Not available	occupational exposure

**Aspiration Hazard**

Name	Value

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

**SECTION 12: Ecological information**

**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

**Chemical fate information**

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

**SECTION 13: Disposal considerations**

**13.1. Disposal methods**

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. The substrate that was abraded must be considered as a factor in the disposal method for this product. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. If no other disposal options are available, waste product



may be placed in a landfill properly designed for industrial waste.

**EPA Hazardous Waste Number (RCRA):** Not regulated

## SECTION 14: Transport Information

Not regulated per U.S. DOT, IATA or IMO.

*These transportation classifications are provided as a customer service. As the shipper YOU remain responsible for complying with all applicable laws and regulations, including proper transportation classification and packaging. 3M transportation classifications are based on product formulation, packaging, 3M policies and 3M understanding of applicable current regulations. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and not the packaging, labeling, or marking requirements. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.*

## SECTION 15: Regulatory information

### 15.1. US Federal Regulations

Contact 3M for more information.

#### 311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - No Delayed Hazard - No

### 15.2. State Regulations

Contact 3M for more information.

### 15.3. Chemical Inventories

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory listing requirements.

Contact 3M for more information.

### 15.4. International Regulations

Contact 3M for more information.

**This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.**

## SECTION 16: Other information

### NFPA Hazard Classification

**Health: 0 Flammability: 1 Instability: 0 Special Hazards: None**

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

**Document Group:** 31-8643-4  
**Issue Date:** 04/14/14

**Version Number:** 1.02  
**Supersedes Date:** 08/23/13

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

**3M USA SDSs are available at [www.3M.com](http://www.3M.com)**