

# **POWER BREEZER™**



- Reduces heat related injuries and increases safety
- Cools up to 3,000 sq. ft. (232 m<sup>2</sup>)
- Reduces temperature by up to 27°F (15°C)
- Water tank can last up to 5 days
- Doesn't get users or equipment wet
- Manages dust and flying insects



Cooling Ability	Up to 27°F (15°C)
Area of Coverage (Optimal)	Up to 3,000 sq. ft. (232m²) INSTANTLY
Effective Distance	Up to 80 feet (24 Meters)
Oscillation	Yes
Integrated Water Container	Yes - 100 gallon (378L). Hose connection not required.
Operating Time	4-5 days running 10-12 hrs/days
Effective Water Vaporization	0.1-2 Gallons/Hour (0.4L-7.6L/Hour)
Electric Consumption	.8-7 Amps; <1,600 Watts running at max power
CFM	14,000
Height	46" (116.8cm) stored, 70" when mounted (177.8cm)
Width	29.5" (75cm)
Depth	42" (107cm)
Weight (without water)	250 lbs (113.4kg)
Power Source	110V
Nozzles	None. No calcification/clogging.
Technology	Unique atomization technology
Highly durable castors	10" (25.4cm) and 8" (20cm) rugged castors
Hard case for shipping and transport	Yes - Integrated into design
Pads used in Swamp Cooler?	Not a swamp cooler. No pads needed. No replacement pads ever necessary.

**THIRD-PARTY ENVIRONMENTAL TESTING:**

MIL-STD 810G  
(Military Standard)



- PASSED  **High Humidity Test**
- PASSED  **Blowing Rain Test**
- PASSED  **Blowing Sand Test**
- PASSED  **Blowing Dust Test**
- PASSED  **High Storage Temp Test**

- OSHA Compliant**
- ETL Certified**  
(USA and Canada)
- NOM Certified**  
(Mexico and some South American countries)



550 SW 12th Avenue, Suite 550  
Deerfield Beach, Florida, 33442

©2015 Breezer Holdings, LLC. All Rights Reserved.  
Power Breezer® is licensed under U.S. Patent No. 6,789,787  
GENPBE15121E

FOR MORE INFORMATION PLEASE CONTACT US:

**POWERBREEZER.COM**  
**INFO@POWERBREEZER.COM**  
**844.233.5673**

