

Half Facepiece Respirators 5000 Series, Disposable


Issue Date 7/1/09

**Pre-assembled for convenience.
Designed for comfort.**

3M™ Half Facepiece Respirators 5000 Series, Disposable are preassembled, have no spare parts and require no maintenance. They offer comfort, convenience and performance against certain organic vapors and/or acid gasses.

Features/Benefits

- Available in 3 sizes (small, medium, large) to comfortably fit many faces
- Ideally suited for:
 - intermittent respirator use
 - plant shutdowns and turnarounds
 - dirty applications where respirators become difficult to clean in a short time
- Resealable storage bag helps keep respirator clean between uses
- Low profile design provides wider field of vision and greater comfort while wearing goggles or glasses
- Lightweight design coupled with cradle suspension helps relieve pressure on back of neck and bridge of nose
- Can be combined with 3M N95, P95 and P100 NIOSH approved filters for airborne particles



3M™ Half Facepiece Respirators 5000 Series, Disposable


Quantitative Fit Test Respirators

3M™ Quantitative Fit Test Respirators are products that provide a simple, direct way to help meet OSHA fit testing requirements. They can be used with any 100 level particulate filter to test face-to-respirator seal. They help satisfy OSHA respiratory protection program requirements and are easily used during respirator training.

| Respirators per bag | Respirators per case |
|---------------------|----------------------|
| 1 | 12 |

These facepieces are for fit test purposes only and are not to be used for respiratory protection.

⚠ WARNING











These respirators help protect against certain airborne contaminants. **Misuse may result in sickness or death.** Before use, the wearer must read and understand *User Instructions* provided as a part of product packaging. Time use limitations may apply. Call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

Important
Before using these respirators, you must determine the following:

1. The type of contaminant(s) for which the respirator is being selected.
2. The concentration level of contaminant(s).
3. Whether the respirator can be properly fitted on the wearer's face. All respirator instructions, warnings and use and time limitations must also be read and understood by the wearer before use.

Before use of these respirators, a written respiratory protection program must be implemented, meeting all the requirements of OSHA 29 CFR 1910.134, including training, medical evaluation and fit testing.

3M™ Filters and Accessories

| | | | | | | | |
|---|---|---|---|--|---|---|---|
|  |  |  |  |  |  |  |  |
| 2071 P95 Filter | 2091/07000 P100 Filter | 2291 P100 Filter | 7093 P100 Filter | 5N11 N95 Filter (Use with the 501 Filter Retainer) | 5P71/07194 P95 Filter (Use with the 501 Filter Retainer) | 501 Filter Retainer (Use with the 5N11 and 5P71 Filters) | 502 Filter Adapter (Use with the 2000 and 2200 Series and 7093 Filters) |

3M™ 5000 Series Respirators

| Product Number | NIOSH Approval* |
|--|---|
| 5101 (Small) 5201 (Medium) 5301 (Large) | Certain organic vapors (a)(b) |
| 5103 (Small) 5203 (Medium) 5303 (Large) | Certain organic vapors, chlorine, hydrogen chloride, and sulfur dioxide or hydrogen sulfide or hydrogen fluoride (a)(b) |

* For respiratory protection against listed contaminants up to 10X PEL.

3M™ 5000 Series Respirator Packout Assemblies

| Product Number | NIOSH Approval* |
|---|--------------------------------------|
| 51P71 (Small) 52P71 (Medium) 53P71 (Large) | P95/Certain organic vapors (a)(b) |

(a) All respirators and respirator/filter assemblies can be used up to the NIOSH approval limits, 10 times the permissible exposure limit, or the maximum use concentration allowable in applicable OSHA standards, whichever is lower.

(b) For specific usage, limitations and warning information, see respirator and/or filter packaging, or call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

| Product Number | Description | Packaging |
|----------------|------------------------------------|-----------|
| 6100Q | Probed Respirator Assembly, Small | 4/Case |
| 6200Q | Probed Respirator Assembly, Medium | 4/Case |
| 6300Q | Probed Respirator Assembly, Large | 4/Case |

NOTE: These devices are to be used exclusively for quantitative fit testing.
Do not use for respiratory protection.



Occupational Health and Environmental Safety Division
3M Center, Building 235-2E-91
St. Paul, MN 55144-1000

For more information, please contact:

3M Occupational Health and Environmental Safety Division (OH&ESD)

In the U.S., contact:

Customer Service
1-800-328-1667

Technical Assistance
1-800-243-4630

Website
www.3M.com/OccSafety

For other 3M products
1-800-3M HELPS

In Canada, contact:

3M Canada Company, OH&ESD
P.O. Box 5757
London, Ontario N6A 4T1

Customer Care
1-800-364-3577

Technical Assistance (Canada only)
1-800-267-4414

Website
www.3M.ca/safety

Technical Assistance In Mexico
01-800-712-0646
5270-2255, 5270-2119 (Mexico City only)
Technical Assistance In Brazil
0800-132333