



Issue date 07-Oct-2015

# Safety Data Sheet

Version 1

## 1. Identification of the Substance/Preparation and of the Company/Undertaking

### Product Identifier

**Product name** CHAMPION SPRAYON PREMIUM INTERIOR/EXTERIOR ENAMEL FLAT WHITE  
**Chemical name** 6-5946-1

### Other means of identification

**Product code** FG 419-0928-2  
**Synonyms** Spray Paint

### Recommended use of the chemical and restrictions on use

**Recommended Use** Interior/exterior enamel.  
**Uses advised against** Do not use on surfaces that come in contact with food.

### Details of the supplier of the safety data sheet

**Supplier Address** Chase Products Co.  
2727 Gardner Road  
Broadview, IL 60155  
708-273-1121

**Manufacturer Address** Chase Products Co.  
2727 Gardner Road  
Broadview, IL 60155  
708-273-1121

### Emergency Telephone Number

**Company Phone Number** 708-865-1000  
**24 Hour Emergency Phone Number** 1-800-255-3924  
**Emergency telephone** ChemTel 1-800-255-3924

## 2. Hazards Identification

### Classification

Acute toxicity - Inhalation (Gases)	Category 4
Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 1B
Reproductive toxicity	Category 2
Specific target organ toxicity (single exposure)	Category 3
Specific target organ toxicity (repeated exposure)	Category 2
Aspiration toxicity	Category 1
FLAMMABLE AEROSOLS	Category 1
Gases Under Pressure	liquefied gas

### Label Elements

### EMERGENCY OVERVIEW

**DANGER**

**hazard statements**  
HARMFUL IF INHALED  
CAUSES SKIN IRRITATION  
Causes serious eye irritation  
May cause genetic defects  
May cause cancer  
Suspected of damaging fertility or the unborn child  
May cause drowsiness or dizziness

May cause damage to organs through prolonged or repeated exposure  
 May be fatal if swallowed and enters airways  
 EXTREMELY FLAMMABLE AEROSOL  
 Contains gas under pressure; may explode if heated



**Appearance** White, viscous liquid

**Physical State** Aerosol

**Odor** Characteristic odor of paint.

**Precautionary Statements - Prevention**

Obtain special instructions before use  
 Do not handle until all safety precautions have been read and understood  
 Wear protective gloves, protective clothing, eye protection and face protection.  
 Use only outdoors or in a well-ventilated area  
 Wash face, hands and any exposed skin thoroughly after handling  
 Do not breathe fumes, mist, vapors or spray.  
 Keep away from heat, sparks, open flames and hot surfaces. — No smoking  
 Pressurized container: Do not pierce or burn, even after use  
 Do not spray on an open flame or other ignition source

**Precautionary Statements - Response**

IF exposed or concerned: Get medical advice/attention  
 Specific treatment: See additional cautionary statements on this label.  
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 If eye irritation persists: Get medical advice/attention  
 IF ON SKIN: Wash with plenty of soap and water  
 If skin irritation occurs: Get medical advice/attention  
 Take off contaminated clothing and wash before reuse  
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
 Call a POISON CENTER or doctor if you feel unwell  
 IF SWALLOWED: Immediately call a POISON CENTER or doctor  
 Do NOT induce vomiting

**Precautionary Statements - Storage**

Store locked up  
 Store in a well-ventilated place. Keep container tightly closed  
 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

**Other Information**

- Harmful to aquatic life with long lasting effects
  - Harmful to aquatic life
- 9.142% of the mixture consists of ingredient(s) of unknown toxicity

**3. Composition/information on Ingredients**

**Synonyms** Spray Paint.  
**Chemical Family** MIXTURES.  
**Formula** 6-5946-1

Chemical name	CAS No	weight-%	Trade secret
---------------	--------	----------	--------------

## FG 419-0928-2 CHAMPION SPRAYON PREMIUM INTERIOR/EXTERIOR ENAMEL FLAT WHITE

Acetone	67-64-1	35-40	*
Propane	74-98-6	15-20	*
N-Butane	106-97-8	10-15	*
Toluene	108-88-3	10-15	*
Titanium Dioxide	13463-67-7	5-10	*
Magnesium Silicate	14807-96-6	5-10	*
Light Aliphatic Naphtha	64742-49-0	1-5	*

\* The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. First aid measures

#### FIRST AID MEASURES

<b>Eye Contact</b>	Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. Call a poison control center or doctor for treatment advice.
<b>Skin contact</b>	Take off contaminated clothing. Rinse skin immediately with plenty of water for 15-20 minutes. Call a poison control center or doctor for treatment advise.
<b>Inhalation</b>	If overcome by vapor, move person to fresh air. If person is not breathing, call 911 or an ambulance, then provide artificial respiration, preferably mouth-to-mouth, if possible. Call a poison control center or doctor for further treatment advise.
<b>Ingestion</b>	Call a poison control center or doctor for treatment advice. Have person sip a glass of water if able to swallow. Do not induce vomiting unless told to do so by a poison control center or doctor. Do not give anything by mouth to an unconscious person.

#### Most important symptoms and effects, both acute and delayed

<b>Symptoms</b>	Acute: Prolonged inhalation of concentrated vapor or mist may cause headaches, dizziness and nausea. Prolonged and repeated contact with skin may cause irritation and reddening. Contact with eyes causes irritation.
-----------------	--

#### Indication of any immediate medical attention and special treatment needed

<b>Note to physicians</b>	Contains petroleum distillates, do not induce vomiting because of aspiration pneumonia hazard.
---------------------------	--

### 5. Fire-fighting measures

#### Suitable extinguishing media

Dry chemical, CO2 or water spray.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

#### Specific hazards arising from the chemical

This product is under pressure. Water spray may be used to cool cans in the vicinity of fire or excessive heat to prevent the explosion of the cans.

**Hazardous combustion products** Thermal decomposition may yield gases like nitrogen oxides, carbon monoxide and carbon dioxide.

#### Explosion data

**Sensitivity to Mechanical Impact** Contents under pressure. This product is extremely flammable. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

**Sensitivity to Static Discharge** Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

#### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**6. Accidental release measures**

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Use in well-ventilated area ONLY. NOTICE: Reports have associated repeated and prolonged occupational over exposure to solvents with permanent brain and nervous system damage. Intentional misuse by deliberately concentrating and inhaling the contents can be harmful or fatal. To avoid breathing vapor or spray mist open windows and doors or use other means to ensure fresh air entry during application and drying. If you experience eye watering, headaches, or dizziness, increase fresh air or wear an appropriate, properly fitted respirator (NIOSH approved), or leave the area. NOTE: Follow respirator manufacturer's instructions carefully for respirator use.

**For emergency responders** Remove all sources of ignition.

**Environmental precautions**

**Environmental precautions** See Section 12 for additional Ecological Information.

**Methods and material for containment and cleaning up**

**Methods for Containment** Provide adequate ventilation to area being treated. Soak up spills with chemically inert, absorbent material.

**Methods for cleaning up** Clean contaminated surface thoroughly.

**7. Handling and Storage**

**Precautions for safe handling**

**Advice on safe handling** Handle as an extremely flammable material. Avoid contact with skin, eyes and clothing. Store cans in a cool, dry place away from heat and open flame.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). **AEROSOL STORAGE LEVEL III (NFPA-30B).**

**Incompatible Materials** Avoid heat, open flame and contact with strong acids, strong bases and strong oxidizers.

**8. Exposure Controls/Personal Protection**

**Control parameters**

**Exposure guidelines** See occupational exposure limits listed below.

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Acetone 67-64-1	STEL: 750 ppm TWA: 500 ppm	TWA: 1000 ppm TWA: 2400 mg/m <sup>3</sup> (vacated) TWA: 750 ppm (vacated) TWA: 1800 mg/m <sup>3</sup> (vacated) STEL: 2400 mg/m <sup>3</sup> The acetone STEL does not apply to the cellulose acetate fiber industry. It is in effect for all other sectors (vacated) STEL: 1000 ppm	IDLH: 2500 ppm TWA: 250 ppm TWA: 590 mg/m <sup>3</sup>
Propane 74-98-6	TWA: 1000 ppm	TWA: 1000 ppm TWA: 1800 mg/m <sup>3</sup> (vacated) TWA: 1000 ppm	IDLH: 2100 ppm TWA: 1000 ppm TWA: 1800 mg/m <sup>3</sup>

**FG 419-0928-2 CHAMPION SPRAYON PREMIUM INTERIOR/EXTERIOR ENAMEL FLAT WHITE**

		(vacated) TWA: 1800 mg/m <sup>3</sup>	
N-Butane 106-97-8	STEL: 1000 ppm	(vacated) TWA: 800 ppm (vacated) TWA: 1900 mg/m <sup>3</sup>	TWA: 800 ppm TWA: 1900 mg/m <sup>3</sup>
Toluene 108-88-3	TWA: 20 ppm	TWA: 200 ppm (vacated) TWA: 100 ppm (vacated) TWA: 375 mg/m <sup>3</sup> (vacated) STEL: 150 ppm (vacated) STEL: 560 mg/m <sup>3</sup> Ceiling: 300 ppm	IDLH: 500 ppm TWA: 100 ppm TWA: 375 mg/m <sup>3</sup> STEL: 150 ppm STEL: 560 mg/m <sup>3</sup>
Titanium Dioxide 13463-67-7	TWA: 10 mg/m <sup>3</sup>	TWA: 15 mg/m <sup>3</sup> total dust (vacated) TWA: 10 mg/m <sup>3</sup> total dust	IDLH: 5000 mg/m <sup>3</sup>
Magnesium Silicate 14807-96-6	TWA: 2 mg/m <sup>3</sup> particulate matter containing no asbestos and <1% crystalline silica, respirable fraction	(vacated) TWA: 2 mg/m <sup>3</sup> respirable dust <1% Crystalline silica, containing no Asbestos TWA: 20 mppcf if 1% Quartz or more, use Quartz limit	IDLH: 1000 mg/m <sup>3</sup> TWA: 2 mg/m <sup>3</sup> containing no Asbestos and <1% Quartz respirable dust
Xylenes (o-, m-, p- isomers) 1330-20-7	STEL: 150 ppm TWA: 100 ppm	TWA: 100 ppm TWA: 435 mg/m <sup>3</sup> (vacated) TWA: 100 ppm (vacated) TWA: 435 mg/m <sup>3</sup> (vacated) STEL: 150 ppm (vacated) STEL: 655 mg/m <sup>3</sup>	-
Ethylbenzene 100-41-4	TWA: 20 ppm	TWA: 100 ppm TWA: 435 mg/m <sup>3</sup> (vacated) TWA: 100 ppm (vacated) TWA: 435 mg/m <sup>3</sup> (vacated) STEL: 125 ppm (vacated) STEL: 545 mg/m <sup>3</sup>	IDLH: 800 ppm TWA: 100 ppm TWA: 435 mg/m <sup>3</sup> STEL: 125 ppm STEL: 545 mg/m <sup>3</sup>

**Appropriate engineering controls**

**Engineering controls**

Use with adequate general or local exhaust ventilation.

**Individual protection measures, such as personal protective equipment**

**Eye/face Protection**

Conventional eyeglasses to guard against splashing.

**Skin and Body Protection**

Chemical resistant gloves required.

**Respiratory protection**

Use in well-ventilated area ONLY. NOTICE: Reports have associated repeated and prolonged occupational over exposure to solvents with permanent brain and nervous system damage. Intentional misuse by deliberately concentrating and inhaling the contents can be harmful or fatal. To avoid breathing vapor or spray mist open windows and doors or use other means to ensure fresh air entry during application and drying. If you experience eye watering, headaches, or dizziness, increase fresh air or wear an appropriate, properly fitted respirator (NIOSH approved), or leave the area. NOTE: Follow respirator manufacturer's instructions carefully for respirator use.

**General hygiene considerations**

Wash hands thoroughly after handling. Wash contaminated clothing before reuse.

**9. Physical and Chemical Properties**

**Information on basic physical and chemical properties**

**Physical State**  
**Appearance**

Aerosol  
White, viscous liquid

**Odor**

Characteristic odor of paint.

**Color**

White

**Odor threshold**

No information available

**Property**

**Values**

**Remarks • Method**

**pH**  
**Melting point/freezing point**  
**Boiling point/boiling range**  
**Flash Point**

Not applicable  
Not applicable  
Acetone 133 F/56.29 C  
Not available. This is an aerosol

Solvent-based product.  
No information available  
No information available  
No information available



**FG 419-0928-2 CHAMPION SPRAYON PREMIUM INTERIOR/EXTERIOR ENAMEL FLAT WHITE**

Chemical name	Oral LD50	dermal LD50	Inhalation LC50
Acetone 67-64-1	= 5800 mg/kg ( Rat )	-	= 50100 mg/m <sup>3</sup> ( Rat ) 8 h
Propane 74-98-6	-	-	= 658 mg/L ( Rat ) 4 h
N-Butane 106-97-8	-	-	= 658 g/m <sup>3</sup> ( Rat ) 4 h
Toluene 108-88-3	= 2600 mg/kg ( Rat )	= 12000 mg/kg ( Rabbit )	= 12.5 mg/L ( Rat ) 4 h
Titanium Dioxide 13463-67-7	> 10000 mg/kg ( Rat )	-	-
Light Aliphatic Naphtha 64742-49-0	> 5000 mg/kg ( Rat )	> 3160 mg/kg ( Rabbit )	= 73680 ppm ( Rat ) 4 h

**Information on toxicological effects**

**Symptoms** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Skin corrosion/irritation** May cause skin irritation and reddening after prolonged or repeated contact with skin.  
**Serious eye damage/eye irritation** Irritating to eyes.  
**irritation** May cause skin and eye irritation.  
**corrosivity** Not applicable.  
**sensitization** No information available.  
**Germ cell mutagenicity** See Section 2 of this SDS.  
**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Toluene 108-88-3		Group 3		
Titanium Dioxide 13463-67-7		Group 2B		X
Magnesium Silicate 14807-96-6		Group 3		

**Reproductive toxicity** See Section 2 of this SDS.  
**STOT - single exposure** No information available.  
**STOT - repeated exposure** No information available.  
**Aspiration Hazard** No information available.

**Numerical measures of toxicity - Product Information**

**Unknown acute toxicity** 9.142% of the mixture consists of ingredient(s) of unknown toxicity  
**The following values are calculated based on chapter 3.1 of the GHS document .**  
**ATEmix (oral)** 21118 mg/kg  
**ATEmix (dermal)** 31293 mg/kg  
**ATEmix (inhalation-gas)** 15680 mg/l  
**ATEmix (inhalation-dust/mist)** 15.9 mg/l  
**ATEmix (inhalation-vapor)** 840 mg/l

**12. Ecological Information**

This product contains chemicals which are listed as a marine pollutants according to DOT.

**ecotoxicity**

42.632% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Toxicity to Microorganisms	Crustacea
Acetone 67-64-1		6210 - 8120: 96 h Pimephales promelas mg/L	EC50 = 14500 mg/L 15 min	10294 - 17704: 48 h Daphnia magna mg/L EC50

**FG 419-0928-2 CHAMPION SPRAYON PREMIUM INTERIOR/EXTERIOR ENAMEL FLAT WHITE**

		LC50 static 4.74 - 6.33: 96 h Oncorhynchus mykiss mg/L LC50 8300: 96 h Lepomis macrochirus mg/L LC50		Static 12600 - 12700: 48 h Daphnia magna mg/L EC50
Toluene 108-88-3	433: 96 h Pseudokirchneriella subcapitata mg/L EC50 12.5: 72 h Pseudokirchneriella subcapitata mg/L EC50 static	15.22 - 19.05: 96 h Pimephales promelas mg/L LC50 flow-through 12.6: 96 h Pimephales promelas mg/L LC50 static 5.89 - 7.81: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 54: 96 h Oryzias latipes mg/L LC50 static 11.0 - 15.0: 96 h Lepomis macrochirus mg/L LC50 static 28.2: 96 h Poecilia reticulata mg/L LC50 semi-static 50.87 - 70.34: 96 h Poecilia reticulata mg/L LC50 static 14.1 - 17.16: 96 h Oncorhynchus mykiss mg/L LC50 static 5.8: 96 h Oncorhynchus mykiss mg/L LC50 semi-static	EC50 = 19.7 mg/L 30 min	5.46 - 9.83: 48 h Daphnia magna mg/L EC50 Static 11.5: 48 h Daphnia magna mg/L EC50
Magnesium Silicate 14807-96-6		100: 96 h Brachydanio rerio g/L LC50 semi-static		
Light Aliphatic Naphtha 64742-49-0				2.6: 96 h Chaetogammarus marinus mg/L LC50

**Persistence and degradability**

No information available.

**Bioaccumulation**

No information available.

Chemical name	Partition coefficient
Acetone 67-64-1	-0.24
Propane 74-98-6	2.3
N-Butane 106-97-8	2.89
Toluene 108-88-3	2.65

**Other adverse effects**

No information available

**13. Disposal Considerations**

**Waste treatment methods**

**Disposal of wastes**

Dispose of in accordance with federal, state and local regulations.

**Contaminated packaging**

Pressurized container: Do not pierce or burn, even after use. Do not puncture or incinerate container. If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency for disposal instructions.

Chemical name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Acetone 67-64-1		Included in waste stream: F039		U002
Toluene 108-88-3	U220	Included in waste streams: F005, F024, F025, F039, K015, K036, K037, K149, K151		U220

Chemical name	RCRA - Halogenated	RCRA - P Series Wastes	RCRA - F Series Wastes	RCRA - K Series Wastes
---------------	--------------------	------------------------	------------------------	------------------------



	<b>Organic Compounds</b>		
Toluene 108-88-3			Toxic waste waste number F025 Waste description: Condensed light ends, spent filters and filter aids, and spent desiccant wastes from the production of certain chlorinated aliphatic hydrocarbons, by free radical catalyzed processes. These chlorinated aliphatic hydrocarbons are those having carbon chain lengths ranging from one to and including five, with varying amounts and positions of chlorine substitution.

Chemical name	California Hazardous Waste Status
Acetone 67-64-1	Ignitable
Toluene 108-88-3	Toxic Ignitable

**14. Transport Information**

**DOT**

<b>UN/ID no</b>	Limited Quantity
<b>Proper Shipping Name</b>	Consumer Commodity
<b>Hazard Class</b>	ORM-D
<b>Marine pollutant</b>	This product contains chemicals which are listed as a marine pollutants according to DOT.

**15. Regulatory information**

**International Inventories**

**TSCA** All ingredients of this product are listed or are excluded from listing under the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.

**DSL** All ingredients are listed or are excluded from listing on the DSL.

**Legend:**

*TSCA - United States Toxic Substances Control Act Section 8(b) Inventory*  
*DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List*

**US Federal Regulations**

**SARA 313**

This product contains the following toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-to-Know Act of 1986 and 40 CFR 372. This information must be included in all SDSs that are copied and distributed for this material.

Chemical name	CAS No	weight-%	SARA 313 - Threshold Values %
Toluene - 108-88-3	108-88-3	10-15	1.0

**SARA 311/312 Hazard Categories**

**Acute Health Hazard** yes



at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**