



Issue date 09-Apr-2015

Safety Data Sheet

Version 1

1. Identification of the Substance/Preparation and of the Company/Undertaking

Product Identifier

Product name CHAMPION'S CHOICE SILICONE MOLD RELEASE SPRAY
Chemical name 7-7784

Other means of identification

Product code FG 438-5162-3
Synonyms Mold releaser

Recommended use of the chemical and restrictions on use

Recommended Use To reduce friction and buildup on molds.
Uses advised against See directions for use on product's label.

Details of the supplier of the safety data sheet

Supplier Address
Chase Products Co.
2727 Gardner Road
Broadview, IL 60155
708-273-1121

Manufacturer Address
Chase Products Co.
2727 Gardner Road
Broadview, IL 60155
708-273-1121

Emergency Telephone Number
Company Phone Number 708-865-1000
24 Hour Emergency Phone Number 1-800-255-3924
Emergency telephone ChemTel 1-800-255-3924

2. Hazards Identification

Classification

Skin corrosion/irritation	Category 2
Aspiration toxicity	Category 1
FLAMMABLE AEROSOLS	Category 1
Gases Under Pressure	liquefied gas

Label Elements

EMERGENCY OVERVIEW

DANGER

hazard statements

CAUSES SKIN IRRITATION
May be fatal if swallowed and enters airways
EXTREMELY FLAMMABLE AEROSOL
Contains gas under pressure; may explode if heated



Appearance Clear liquid that will be

Physical State Aerosol

aerosolized.

Odor Petroleum hydrocarbon odor.

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves, protective clothing, eye protection and face protection.
 Keep away from heat, sparks, open flames and hot surfaces. — No smoking
 Pressurized container: Do not pierce or burn, even after use
 Do not spray on an open flame or other ignition source

Precautionary Statements - Response

Specific treatment: See additional cautionary statements on this label.
 IF ON SKIN: Wash with plenty of soap and water
 If skin irritation occurs: Get medical advice/attention
 Take off contaminated clothing and wash before reuse
 IF SWALLOWED: Immediately call a POISON CENTER or doctor.
 Do NOT induce vomiting

Precautionary Statements - Storage

Store locked up
 Protect from sunlight. Store in a well-ventilated place
 Do not expose to temperatures exceeding 50°C (122 °F)

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Other Information

• Toxic to aquatic life with long lasting effects
 0% of the mixture consists of ingredient(s) of unknown toxicity

3. Composition/information on Ingredients

Synonyms Mold releaser.
Chemical Family MIXTURES.
Formula 7-7784

Chemical name	CAS No	weight-%	Trade secret
n-butane	106-97-8	55-60	*
Propane	74-98-6	20-25	*
Heptane	142-82-5	15-20	*

* The exact percentage (concentration) of composition has been withheld as a trade secret.

4. First aid measures

FIRST AID MEASURES

Eye Contact Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. Call a poison control center or doctor for treatment advice.

Skin contact In case of contact, immediately flush skin with plenty of water. Wash skin with soap and water. If irritation develops, consult a physician.

inhalation If overcome by vapor, move person to fresh air. If person is not breathing, call 911 or an ambulance, then provide artificial respiration, preferably mouth-to-mouth, if possible. Call a poison control center or doctor for further treatment advise.

INGESTION Ingestion from an aerosol product is unlikely to occur. Contains petroleum distillates. Harmful if swallowed. If accidentally swallowed, do not induce vomiting, call physician immediately.

Most important symptoms and effects, both acute and delayed

Symptoms Acute: Prolonged inhalation of concentrated vapor or mist may cause headaches, dizziness and nausea. Prolonged and repeated contact with skin may cause irritation and reddening. Contact with eyes causes irritation.

Indication of any immediate medical attention and special treatment needed

Note to physicians Contains petroleum distillates, do not induce vomiting because of aspiration pneumonia hazard.

5. Fire-fighting measures

Suitable extinguishing media

Dry chemical, CO2 or water spray.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

This product is under pressure. Water spray may be used to cool cans in the vicinity of fire or excessive heat to prevent the explosion of the cans.

Hazardous combustion products Thermal decomposition may release carbon monoxide and carbon dioxide.

Explosion data

Sensitivity to Mechanical Impact Contents under pressure, keep away from heat and open flame.

Sensitivity to Static Discharge Keep away from heat, sparks, flame, and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Use with adequate general or local exhaust ventilation.

For emergency responders Remove all sources of ignition.

Environmental Precautions

Environmental Precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for Containment Provide adequate ventilation to area being treated. Soak up spills with chemically inert, absorbent material.

Methods for cleaning up Clean contaminated surface thoroughly.

7. Handling and Storage

Precautions for safe handling

Advice on safe handling Do not deliberately inhale vapor or spray mist. Avoid getting spray into eyes. Keep out of reach of children.

Conditions for safe storage, including any incompatibilities

FG 438-5162-3 CHAMPION'S CHOICE SILICONE MOLD RELEASE SPRAY

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). **AEROSOL STORAGE LEVEL III (NFPA-30B).**

Incompatible Materials Avoid heat, open flame and contact with strong oxidizers.

8. Exposure Controls/Personal Protection

Control parameters

Exposure guidelines See occupational exposure limits listed below.

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
n-butane 106-97-8	STEL: 1000 ppm	(vacated) TWA: 800 ppm (vacated) TWA: 1900 mg/m ³	TWA: 800 ppm TWA: 1900 mg/m ³
Propane 74-98-6	TWA: 1000 ppm	TWA: 1000 ppm TWA: 1800 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1800 mg/m ³	IDLH: 2100 ppm TWA: 1000 ppm TWA: 1800 mg/m ³
Heptane 142-82-5	STEL: 500 ppm TWA: 400 ppm	TWA: 500 ppm TWA: 2000 mg/m ³ (vacated) TWA: 400 ppm (vacated) TWA: 1600 mg/m ³ (vacated) STEL: 500 ppm (vacated) STEL: 2000 mg/m ³	IDLH: 750 ppm Ceiling: 440 ppm 15 min Ceiling: 1800 mg/m ³ 15 min TWA: 85 ppm TWA: 350 mg/m ³

Appropriate engineering controls

Engineering controls Use with adequate general or local exhaust ventilation.

Individual protection measures, such as personal protective equipment

Eye/face Protection Conventional eyeglasses to guard against splashing.

Skin and Body Protection Neoprene or rubber gloves required.

Respiratory protection Use in a well-ventilated area ONLY. **WHEN USING INDOORS, KEEP WINDOWS AND DOORS OPEN UNTIL FUMES DISSIPATE.**

General hygiene considerations Wash hands thoroughly after handling.

9. Physical and Chemical Properties

Information on basic physical and chemical properties

Physical State	Aerosol	Odor	Petroleum hydrocarbon odor.
Appearance	Clear liquid that will be aerosolized.	Odor threshold	No information available
Color	clear		
Property	Values	Remarks • Method	
pH	Not applicable	Solvent-based product.	
Melting point/freezing point	Not applicable	No information available	
Boiling point/boiling range	Heptane 210 °F/ 93.3 °C	No information available	
Flash Point	Not Available. This is an aerosol product for which Flame Projection is over 18 inches with 8 in flashback. Temperatures above 120 F may cause cans to burst.	No information available	
Evaporation Rate	Faster than butyl acetate	No information available	
Flammability (solid, gas)		No information available	
Flammability Limits in Air		No information available	
Upper flammability limits	Not available		
Lower Flammability Limit	Not available		

Vapor pressure		No information available
Vapor Density		No information available
Specific gravity	0.735 g/ml concentrate	No information available
Water solubility	Insoluble in water	No information available
Solubility in other solvents		No information available
Partition coefficient		No information available
Autoignition Temperature		No information available
Decomposition temperature		No information available
Kinematic viscosity		No information available
Dynamic viscosity		No information available
Explosive properties	No information available	
Oxidizing properties	No information available	

Other Information

Softening point	No information available
Molecular weight	No information available
VOC content (%)	97.0
Density	6.12 lb/gal
Bulk Density	No information available

10. Stability and Reactivity

Reactivity

Not applicable
no data available

Chemical stability

Stable.

Possibility of hazardous reactions

Temperatures above 130 °F may cause cans to burst with force.

hazardous polymerization Hazardous polymerization does not occur.

Conditions to Avoid

Temperatures above 122 °F (50 °C).

Incompatible Materials

Avoid heat, open flame and contact with strong oxidizers.

Hazardous decomposition products

Thermal decomposition may yield gases like carbon monoxide and carbon dioxide.

11. Toxicological Information

Information on likely routes of exposure

Product Information This product has not been tested as whole. See below for information on ingredients.

inhalation no data available.

Eye Contact no data available.

Skin contact no data available.

INGESTION no data available.

Chemical name	Oral LD50	dermal LD50	Inhalation LC50
n-butane 106-97-8	-	-	= 658 g/m ³ (Rat) 4 h
Propane 74-98-6	-	-	= 658 mg/L (Rat) 4 h
Heptane 142-82-5	-	= 3000 mg/kg (Rabbit)	= 103 g/m ³ (Rat) 4 h

Information on toxicological effects

Symptoms Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation May cause skin irritation and reddening after prolonged or repeated contact with skin.
Serious eye damage/eye irritation Irritating to eyes.
irritation May cause skin and eye irritation.
corrosivity Not applicable.
sensitization No information available.
Germ Cell Mutagenicity No information available.
carcinogenicity Over exposure to petroleum solvents has been associated with nervous system damage.

Reproductive Toxicity No information available.
STOT - single exposure No information available.
STOT - repeated exposure No information available.
Aspiration Hazard No information available.

Numerical measures of toxicity - Product Information

Unknown acute toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity
The following values are calculated based on chapter 3.1 of the GHS document .
ATEmix (oral) 5612 mg/kg
ATEmix (dermal) 17647 mg/kg
ATEmix (inhalation-gas) 700 mg/l
ATEmix (inhalation-dust/mist) 606 mg/l
ATEmix (inhalation-vapor) 349 mg/l

12. Ecological Information

Contains heptane which is toxic to aquatic life.

ecotoxicity

83% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Toxicity to Microorganisms	Crustacea
Heptane 142-82-5		375.0: 96 h Cichlid fish mg/L LC50		10: 24 h Daphnia magna mg/L EC50

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical name	Partition coefficient
n-butane 106-97-8	2.89
Propane 74-98-6	2.3
Heptane 142-82-5	4.66

Other adverse effects No information available

13. Disposal Considerations

Waste treatment methods

FG 438-5162-3 CHAMPION'S CHOICE SILICONE MOLD RELEASE SPRAY

Disposal of wastes	Dispose of in accordance with federal, state and local regulations.
Contaminated packaging	Pressurized container: Do not pierce or burn, even after use. Do not puncture or incinerate container. If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency for disposal instructions.

Chemical name	California Hazardous Waste Status
Heptane 142-82-5	Toxic Ignitable

14. Transport Information

DOT	Limited quantity (LQ) Silicone mold release
UN/ID no	UN1950
Proper Shipping Name	Limited quantity (LQ)
Hazard Class	2.1
Marine pollutant	Contains heptane which is toxic to aquatic life.

15. Regulatory information

International Inventories

TSCA	All ingredients of this product are listed or are excluded from listing under the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.
DSL	All ingredients are listed or are excluded from listing on the DSL.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	yes
Chronic Health Hazard	No
Fire Hazard	yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
n-butane 106-97-8	X	X	X
Propane 74-98-6	X	X	X
Heptane 142-82-5	X	X	X

U.S. EPA Label information

EPA Pesticide registration number Not applicable

16. Other information

NFPA	Health Hazards 2	Flammability 4	Instability 1	Physical and chemical properties Not applicable Personal Protection B
HMIS	Health Hazards 2	Flammability 4	Physical Hazards 1	

Prepared by Regulatory Department
Issue date 09-Apr-2015

Revision note

This SDS supersedes a previous MSDS dated July 12, 2005.

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet