


# Half and Full Facepiece Respirators 7000 Series, Ultimate Reusable

**Issue Date 01/01/04** 

3M<sup>™</sup> Half and Full Facepiece Respirators 7000 Series, Ultimate Reusable are NIOSH approved to accommodate a wide variety of cartridges and filters. These respirators are both made with silicone to provide maximum comfort and durability. The half and full facepieces are each available in 3 sizes (small, medium, large) to comfortably fit many faces.

## 3M™ Half Facepiece Respirator 7500, Ultimate Reusable

- Valve design helps make breathing easier, and helps reduce heat and moisture buildup in facepiece.
- Advanced silicone material provides a softer feel on the face.
- Unique head harness design adjusts easily and user has the option of wearing the respirator in either traditional or drop-down mode.



3M™ Half and Full Facepiece Respirators 7000 Series, Ultimate Reusable

## 3M<sup>™</sup> Full Facepiece Respirator 7800S, Ultimate Reusable

- Available in many configurations ranging from negative pressure air purifying to SCBA. Excellent choice for standardizing your entire facility's respiratory requirements.
- Extra-large inhalation and exhalation valves help make breathing easier.
- Double-flange faceseal and six adjustable straps help provide a secure fit.

#### **AWARNING**



These respirators help reduce exposure to certain airborne contaminants. **Misuse may result in sickness or death.** Before use, the wearer must read and understand *User Instructions* provided as a part of product packaging. Time use limitations may apply. Call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.

#### **Important**


Before using these respirators, you must determine the following:

- 1. The type of contaminant(s) for which the respirator is being selected.
- 2. The concentration level of contaminant(s).
- Whether the respirator can be properly fitted on the wearer's face. All respirator instructions, warnings and use and time limitations must also be read and understood by the wearer before use.

Before use of these respirators, a written respiratory protection program must be implemented, meeting all the requirements of OSHA 29 CFR 1910.134, including training, medical evaluation and fit testing.


# 3M<sup>™</sup> Half and Full Facepiece Respirators 7000 Series, Ultimate Reusable

3M™ Half and Full Facepieces 7000 Series (all filters, cartridges and retainers are sold separately)



#### **Half Facepieces**


7501 Small 7502 Medium 7503 Large



#### **Full Facepieces**

7800S Small 7800S Medium 7800S Large

#### 3M™ Filters and Accessories 2000 Series, 7093, 5N11, 5P71





7093 P100 particulate filter



5N11 N95 filter (use with the 501 filter retainer)



5P71/07194 P95 filter (use with the 501 filter retainer)



filter retainer (use with the 5N11 and 5P71 filters)



502 filter adapter (use with the 2000 Series and 7093 filters)

#### 3M™ Cartridges 6000 Series

Product Number	NIOSH Approval <sup>2</sup>		Product Number	NIOSH Approval <sup>2</sup>		
6001	Certain organic vapors	6	60921	P100/Certain organic vapors		
6002	Chlorine, hydrogen chloride, and sulfur dioxic chlorine dioxide or hydrogen sulfide (escape		60922	P100/Chlorine, hydrogen chloride, and sulfu or chlorine dioxide or hydrogen sulfide (esc		
6003	Certain organic vapors, chlorine, hydrogen chloride, and sulfur dioxide or hydrogen sulfide (escape only) or hydrogen fluoride		60923	P100/Certain organic vapors, chlorine, hydrogen chloride, and sulfur dioxide or hydrogen sulfide (escape only) or hydrogen fluoride		
6004	Ammonia and methylamine		60924	P100/Ammonia and methylamine		
6005	Formaldehyde <sup>3</sup> and certain organic vapors		60925	P100/Formaldehyde <sup>3</sup> and certain organic	vapors	
6006	Certain organic vapors, chlorine, hydrogen chloride, chlorine dioxide, sulfur dioxide, hydrogen sulfide (escape only) ammonia/methylamine, formaldehyde³ or hydrogen fluoride		60926	P100/Certain organic vapors, chlorine, hydrogen chloride, chlorine dioxide, sulfur dioxide, hydrogen sulfide (escape only) ammonia/methylamine, formaldehyde³ or hydrogen fluoride		
6009	Mercury vapor or chlorine gas		60928	P100/Organic Vapor/Acid Gas <sup>4</sup>		
			60929	P100/Mercury vapor or chlorine gas		

- <sup>1</sup> Nuisance levels refer to concentrations below the OSHA PEL.
- <sup>2</sup> For respiratory protection against the following contaminants up to 10X PEL with half facepiece respirators or 50X PEL with full facepiece respirators when quantitatively fit tested.
- 3 OSHA regulations require that gas-proof goggles be worn with half facepiece respirators when used against formaldehyde.
- <sup>4</sup> As recommended by the California Department of Pesticide Regulation No. 01-099 Methyl Bromide Field Fumigation.


### 3M<sup>™</sup> Half and Full Facepiece Respirators 7000 Series, Ultimate Reusable

#### 3M<sup>™</sup> Half Facepiece 7500 Series Replacement Parts

7581	Head Harness Assembly	7583	Exhalation Valve
7582	Inhalation Valve	7586	Cartridge Filter Holder

#### 3M<sup>™</sup> Full Facepiece 7800S Series Replacement Parts

701	Cartridge/Filter Adapter	7890	Full Face Plug	7925	Spectacle Kit
6895	Inhalation Gasket	7891	Cartridge Holder	7981S	Small Nose Cup Assembly,
7282	Inhalation Valve	7893S	Head Strap Assembly, Silicone		Silicone
7283	Exhalation Valve	7894	Eyeglass Frame and Mount	7986	Tinted Lens Cover
7881S	Nose Cup Assembly, Silicone	7895	Speaking Diaphragm Kit	7989	Full Facepiece Button
7882	Nose Cup Valve Assembly	7899-25	Lens Cover (25 pack)	7990	Clip-On Welding Faceshield Kit
7883	Neck Strap Assembly	7899-100	Lens Cover (100 pack)	7991	Electronic Lens Assembly
7884	Lens	7914	Band Clamp	7992	Lens Gasket
7885	Lens Frame Kit	7915-5	Tyvek® Shroud	7993	Welder's Shroud
7886	Removable DIN Connector	7916-5	Breathing Room Assembly	7999	Air Inlet Gasket
7887	Inhalation Port Gasket	7918	Exhalation Valve Cover		



#### 3M™ Quantitative Fit Test Adapter 601

For 3M 6000 and 7000 Series respirators with bayonet attachment.

#### Half Facepiece 7500 Series

Facepieces per box	Facepieces per case
1	10

#### Full Facepiece 7800S Series

Facepieces per box	Facepieces per case
1	1

Tyvek is a registered trademark of DuPont.

### 3M<sup>™</sup> Fit Test Kits

- FT-10 Qualitative Fit Test Apparatus (sweet solution) includes:
  - FT-11 Sensitivity Solution (sweet)
  - FT-12 Fit Test Solution (sweet)
  - FT-13 Nebulizer (2 pack)
  - FT-14 Fit Test Hood
  - FT-15 Collar
- FT-20 Training and Fit Testing Case (sweet solution) includes:
  - FT-10 Materials
  - Universal Fitting Video
  - Animated Guide to Respiratory Protection Video
  - Fitting Posters
- FT-30 Qualitative Fit Test Apparatus (bitter solution) includes:
  - FT-13 Nebulizer (2 pack
  - FT-14 Fit Test Hood
  - FT-15 Collar
  - FT-31 Sensitivity Solution (bitter)
  - FT-32 Fit Test Solution (bitter)

#### For more information, please contact:

#### 3M Occupational Health and **Environmental Safety Division** (OH&ESD)

#### In the U.S., contact:

Sales Assistance

1-800-896-4223

**Technical Assistance** 1-800-243-4630

**Fax On Demand** 

1-800-646-1655

Internet

http://www.3M.com/occsafety

For other 3M products

1-800-3M HELPS

#### In Canada, contact:

3M Canada Company, OH&ESD P.O. Box 5757

London, Ontario N6A 4T1

Sales Assistance

1-800-265-1840, ext. 6137

Technical Assistance (Canada only)

1-800-267-4414

**Fax On Demand** 

1-800-646-1655

Internet

http://www.3M.com/CA/occsafety

#### **Technical Assistance In Mexico**

01-800-712-0646

5270-2255, 5270-2119 (Mexico City only)

**Technical Assistance In Brazil** 0800-132333

Fax On Demand O.U.S. Locations 1-651-732-6530

3M Occupational Health and Environmental Safety Division

3M Center, Building 235-2W-70 St. Paul, MN 55144-1000