



MECHANICAL ACCESS WITH LEVER HANDLE

CL400

Medium-duty mechanical locks with full size lever handles, allowing use as the primary lock on doors where a knob-operated lock would be unsuitable.

The CL400 range of mechanical locks offer a variety of functions. Allows the user flexibility on how to manage entry by code or Passage Function entry. The inside lever handle will retract the latchbolt so avoiding accidentally locking a person in the room. Front and back plates can be purchased for use with existing locks.

FEATURES


- Medium-duty Codelock
- PVD weather resistant, low maintenance finish
- Full size lever handles
- Four options available
- 8,191 non sequential codes available
- Passage Function option available
- Tubular Latch
- Available in stainless steel or polished brass finish
- Suitable for internal and external use
- Limited lifetime guarantee*



CL400

Front and Back Plates

Front and back plates only for use with existing tubular latch lock.



CL410

Tubular Latch

Medium-duty tubular latch locks. Stainless steel latchbolt head with 'anti' shim deadlocking plunger, 5/16" follower. The outside lever handle will retract the latch after a correct code is entered. The spring loaded latchbolt will lock automatically when the door is closed.

OPTIONS

Latch Options:

2 3/8" backset requires 1" edge and cross-bore holes, minimum door stile 3 1/4". With use of included trim plates, will cover 161 USA door prep. 2 3/4" backset, requires 1" edge and cross-bore holes, minimum door stile 3 5/16".

Back to Back Option (BB):

Two coded plates for installation on both sides of the door. Provides coded access in both directions.

Passage Function Option:


The outside lever will retract the latchbolt without using a code.

For further product model options see price list.

PRODUCT DIMENSIONS

CL400

CL410



Code Change Method

Requires removal of lock from door. Locks are supplied with a random code commencing with the 'C' clear button. To change the code after fitting, the lock must first be removed from the door. The code is non sequential, i.e. the code can be entered in any preferred order (e.g. 1234 can be 4321 or 1342). A total of 8,191 different codes are available - any of which can be entered in any order.

TECHNICAL SPECIFICATIONS

Options	Four available
Spindle Type	Two part 5/16" spring loaded spindle
Material	Zinc Alloy
Door Thickness	1 3/8" - 2 1/2"
Buttons	14 stainless steel buttons
Non Handed	Locks will fit doors hung on the left or right
Fitting Options	Vertical
Finish	PVD (Physical Vapor Deposition) hardwearing low maintenance finishes SS (stainless steel) and PB (polished brass)
Codes	8,191 non sequential codes available
Code Storage	Single Code
Suitable For	Internal and external use

*Codelocks mechanical locks will be repaired, serviced or replaced free of charge if they develop a manufacturing fault. Faults caused by misuse, abuse and/or poor fitting are not covered by the guarantees.

