

AL752BBISSTB



32" x 23.63" x 23.5" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose use, auto defrost w/SS wrapped door, towel bar handle, and black cabinet

Highlights:

32" height for use under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Automatic defrost ensures minimum user maintenance

Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished black cabinet	Allows the unit to be used freestanding
Stainless steel door	Durable design with lasting elegance
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Automatic defrost	Reduced user maintenance with automatic defrost operation
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior

AL752BBISSTB Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.75"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	88.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	26.25"
Interior Width	21.0"
Interior Depth	17.75"
Compressor Step Height	5.5"

Compressor Step Width
Compressor Step Depth

