

AL752BSSTB



32" x 23.63" x 23.5" (H x W x D)

ADA compliant all-refrigerator for freestanding general purpose use, auto defrost w/SS door, towel bar handle, and black cabinet

Highlights:

32" height for use in ADA compliant settings

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Automatic defrost ensures minimum user maintenance

Product Features:

ADA compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Automatic defrost	Reduced user maintenance with automatic defrost operation
Stainless steel door	Durable construction brings modern luxury to any setting
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Adjustable thermostat	Dial thermostat located inside for easy temperature management
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient rocker switch located just behind the thermostat
Deep shelf space	Interior accommodates large trays up to 19 1/2" x 15 1/2"

AL752BSSTB Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.25"
Depth with door at 90°	45.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	88.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	26.25"
Interior Width	21.0"
Interior Depth	17.75"
Compressor Step Height	5.5"

Compressor Step Width
Compressor Step Depth

