



## Safety Data Sheet

# Big D Deodorant Concentrate, Cherry

### SECTION 1. IDENTIFICATION

|                                      |  |
|--------------------------------------|--|
| <b>Product Identifier</b>            | Big D Deodorant Concentrate, Cherry  |
| <b>Other Means of Identification</b> | 121300, 321300, 421300, 521300, & C0421303   |
| <b>Other Identification</b>          | Deodorant Concentrate, Cherry  |
| <b>Product Family</b>                | Liquid Deodorants  |
| <b>Recommended Use</b>               | Deodorant.   |
| <b>Restrictions on Use</b>           | None known.  |
| <b>Manufacturer</b>                  | Big D Industries, Inc., 5620 SW 29th St, Oklahoma City, OK, 73179, 405 682 2541, BigDInd.com |
| <b>Supplier</b>                      | Big D Industries, Inc., 5620 SW 29th St, Oklahoma City, OK, 73179, 405 682 2541, BigDInd.com |
| <b>Emergency Phone No.</b>           | Big D Industries, 800 535 5053, 24hr (Infotrac)  |
| <b>SDS No.</b>                       | 0408   |

### SECTION 2. HAZARDS IDENTIFICATION

#### GHS Classification

Serious eye damage/eye irritation - Category 1

#### GHS Label Elements



Signal Word:  
Danger

Hazard Statement(s):  
Causes serious eye damage.

Precautionary Statement(s):  
Prevention:  
Wear eye protection/face protection.

Response:  
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
Immediately call a POISON CENTRE/doctor.

---

|                      |                                     |
|----------------------|-------------------------------------|
| Product Identifier:  | Big D Deodorant Concentrate, Cherry |
| SDS No.:             | 0408                                |
| Date of Preparation: | March 27, 2015                      |

Storage:  
Store in accordance with local, regional, national and international regulations.

Disposal:  
Dispose of contents/container in accordance with local, regional, national and international regulations.

**Other Hazards**

None known.

### SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Mixture:

| Chemical Name   | CAS No.    | %     | Other Identifiers |
|---|------------|-------|-------------------|
| Other components below reportable Levels              | No CAS     | 92.76 |                   |
| Poly(oxy-1,2-ethanediyl), alpha-octyl- omega-hydroxy- | 27252-75-1 | 3.50  |                   |
| 2-Propanol  | 67-63-0    | 1.81  |                   |
| Benzaldehyde  | 100-52-7   | 0.92  |                   |
| Dipropylene glycol monomethyl ether                   | 34590-94-8 | 0.48  |                   |
| Ethyl acetate   | 141-78-6   | 0.23  |                   |
| Benzyl acetate  | 140-11-4   | 0.15  |                   |
| n-Amyl acetate  | 628-63-7   | 0.15  |                   |

### SECTION 4. FIRST-AID MEASURES

**First-aid Measures**

**Inhalation**

Move to fresh air.

**Skin Contact**

Wash gently and thoroughly with lukewarm, gently flowing water and mild soap for 5 minutes.

**Eye Contact**

Immediately rinse the contaminated eye(s) with lukewarm, gently flowing water for 15-20 minutes, while holding the eyelid(s) open.

**Ingestion**

Call a Poison Centre or doctor if you feel unwell or are concerned. Rinse mouth with water.

**Most Important Symptoms and Effects, Acute and Delayed**

If on skin:

May cause mild irritation.

**Immediate Medical Attention and Special Treatment**

**Special Instructions**

Not applicable.

**Medical Conditions Aggravated by Exposure**

None known.

### SECTION 5. FIRE-FIGHTING MEASURES

**Extinguishing Media**

**Suitable Extinguishing Media**

Not combustible. Use extinguishing agent suitable for surrounding fire.

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

### Unsuitable Extinguishing Media

None known.

### Specific Hazards Arising from the Chemical

Does not burn.

This product presents no unusual hazards in a fire situation.

Not known to generate any hazardous decomposition products in a fire.

### Special Protective Equipment and Precautions for Fire-fighters

No special precautions are necessary.

Chemical protective clothing (e.g. chemical splash suit) and positive pressure SCBA may be necessary.

## SECTION 6. ACCIDENTAL RELEASE MEASURES

### Personal Precautions, Protective Equipment, and Emergency Procedures

No special precautions are necessary.

### Environmental Precautions

It is good practice to prevent releases into the environment.

### Methods and Materials for Containment and Cleaning Up

Contain and soak up spill with absorbent that does not react with spilled product.

## SECTION 7. HANDLING AND STORAGE

### Precautions for Safe Handling

No special handling precautions are necessary.

### Conditions for Safe Storage

No special requirements for storage area.

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

| Chemical Name                       | ACGIH TLV® |         | OSHA PEL   |         | AIHA WEEL |     |
|-------------------------------------|------------|---------|------------|---------|-----------|-----|
|                                     | TWA        | STEL    | TWA        | Ceiling | 8-hr TWA  | TWA |
| 2-Propanol                          | 200 ppm    | 400 ppm | 980 mg/m3  |         |           |     |
| Dipropylene glycol monomethyl ether | 100 ppm    | 150 ppm | 600 mg/m3  |         |           |     |
| Ethyl acetate                       | 400 ppm    |         | 1400 mg/m3 |         |           |     |
| Benzyl acetate                      | 10 ppm     |         |            |         |           |     |
| n-Amyl acetate                      | 50 ppm     | 100 ppm | 525 mg/m3  |         |           |     |

ACGIH® = American Conference of Governmental Industrial Hygienists. TWA = Time-Weighted Average. STEL = Short-term Exposure Limit.

### Appropriate Engineering Controls

The hazard potential of this product is relatively low. General ventilation is usually adequate.

### Individual Protection Measures

#### Eye/Face Protection

Not required but it is good practice to wear safety glasses or chemical safety goggles.

#### Skin Protection

Not required, if used as directed.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

### Basic Physical and Chemical Properties

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

|   |   |
|---|---|
| <b>Appearance</b>                                       | liquid. Particle Size: Not applicable                                 |
| <b>Odour</b>  | Fragrant (Fragrance)  |
| <b>Odour Threshold</b>                                  | Not available   |
| <b>pH</b>   | Not available   |
| <b>Melting Point/Freezing Point</b>                     | Not available (melting); Not available (freezing)                     |
| <b>Initial Boiling Point/Range</b>                      | > 212 °F (100 °C)   |
| <b>Flash Point</b>                                      | > 200 °F (93 °C) (closed cup)   |
| <b>Evaporation Rate</b>                                 | Not available   |
| <b>Flammability (solid, gas)</b>                        | Not applicable  |
| <b>Upper/Lower Flammability or Explosive Limit</b>      | Not available (upper); Not available (lower)                          |
| <b>Vapour Pressure</b>                                  | Not available   |
| <b>Vapour Density (air = 1)</b>                         | Not available   |
| <b>Relative Density (water = 1)</b>                     | ~ 1 at 68 °F (20 °C)  |
| <b>Solubility</b>                                       | Soluble in all proportions in water; Not available (in other liquids) |
| <b>Partition Coefficient, n-Octanol/Water (Log Kow)</b> | Not available   |
| <b>Auto-ignition Temperature</b>                        | Not available   |
| <b>Decomposition Temperature</b>                        | Not available   |
| <b>Viscosity</b>  | Not available (kinematic)   |
| <b>Other Information</b>                                |   |
| <b>Physical State</b>                                   | Liquid  |
| <b>Molecular Formula</b>                                | Not applicable  |
| <b>Molecular Weight</b>                                 | Not applicable  |
| <b>Bulk Density</b>                                     | Not available   |
| <b>Surface Tension</b>                                  | Not available   |
| <b>Critical Temperature</b>                             | Not available   |
| <b>Electrical Conductivity</b>                          | Not available   |
| <b>Vapour Pressure at 50 deg C</b>                      | Not available   |
| <b>Saturated Vapour Concentration</b>                   | Not available   |

## SECTION 10. STABILITY AND REACTIVITY

### Reactivity

None known.

### Chemical Stability

Normally stable.

### Possibility of Hazardous Reactions

None known.

### Conditions to Avoid

None known.

### Incompatible Materials

None known.

### Hazardous Decomposition Products

None known.

## SECTION 11. TOXICOLOGICAL INFORMATION

### Likely Routes of Exposure

Skin contact; eye contact; ingestion; inhalation.

### Acute Toxicity

| Chemical Name                       | LC50                     | LD50 (oral)                        | LD50 (dermal)             |
|-------------------------------------|--------------------------|------------------------------------|---------------------------|
| 2-Propanol                          | 72.6 mg/L (rat) (vapour) | 4396 mg/kg (rat)                   | 12870 mg/kg (rabbit)      |
| Dipropylene glycol monomethyl ether |                          | 5135 mg/kg                         | 9500 mg/kg                |
| Benzaldehyde                        |                          | > 1300 mg/kg (rat)                 | > 2000 mg/kg (guinea pig) |
| Ethyl acetate                       | 16000 mg/L (rat)         | 5600 mg/m3 (rat) (2-hour exposure) |                           |
| Benzyl acetate                      |                          | 830 mg/kg (mouse)                  | > 5000 mg/kg (rabbit)     |

### Skin Corrosion/Irritation

No information was located.

### Serious Eye Damage/Irritation

No information was located.

### STOT (Specific Target Organ Toxicity) - Single Exposure

#### Inhalation

No information was located.

#### Skin Absorption

No information was located.

#### Ingestion

No information was located.

### Aspiration Hazard

No information was located.

### STOT (Specific Target Organ Toxicity) - Repeated Exposure

No information was located.

### Respiratory and/or Skin Sensitization

No information was located.

### Carcinogenicity

| Chemical Name | IARC | ACGIH® | NTP | OSHA |
|---------------|------|--------|-----|------|
| 2-Propanol    |      | A4     |     |      |

ACGIH®: A4 – Not classifiable as a human carcinogen.

### Reproductive Toxicity

#### Development of Offspring

No information was located.

#### Sexual Function and Fertility

No information was located.

#### Effects on or via Lactation

No information was located.

### Germ Cell Mutagenicity

No information was located.

### Interactive Effects

No information was located.

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

## SECTION 12. ECOLOGICAL INFORMATION

Environmental information was not located.

### Toxicity

#### Acute Aquatic Toxicity

| Chemical Name  | LC50 Fish  | EC50 Crustacea   | ErC50 Aquatic Plants | ErC50 Algae              |
|--|--|--|----------------------|--------------------------|
| 2-Propanol   | 9640 mg/L<br>(Pimephales<br>promelas (fathead<br>minnow); 96-hour) | 13299 mg/L<br>(Daphnia magna<br>(water flea); 48-hour) |                      | > 1000 mg/L<br>(96-hour) |
| Poly(oxy-1,2-ethanediyl),<br>alpha-octyl- omega<br>-hydroxy- |  | > 100 mg/L (Daphnia<br>magna (water flea);<br>48-hour) |                      |                          |
| Benzaldehyde   | 0.8-1.44 mg/L<br>(Lepomis<br>macrochirus<br>(bluegill); 96-hour)   |  |                      |                          |
| Ethyl acetate  | 200.32-225.42 mg/L<br>(48-hour)                                    |  |                      |                          |
| n-Amyl acetate   | 65 mg/L (96-hour)  |  |                      |                          |

## SECTION 13. DISPOSAL CONSIDERATIONS

### Disposal Methods

This product is a non-hazardous waste.

## SECTION 14. TRANSPORT INFORMATION

Not regulated under Canadian TDG Regulations. Not regulated under US DOT Regulations.

**Special Precautions for User** Not applicable

**Transport in Bulk According to Annex II of MARPOL 73/78 and the IBC Code**

Not applicable

## SECTION 15. REGULATORY INFORMATION

### Safety, Health and Environmental Regulations

#### Canada

#### WHMIS Classification



Class D2B

D2B - Toxic (Eye irritant)

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all of the information required by the Controlled Products Regulations.

#### Domestic Substances List (DSL) / Non-Domestic Substances List (NDSL)

All ingredients are listed on the DSL or are not required to be listed.

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

**CEPA - National Pollutant Release Inventory (NPRI)**

Part 1A. (Polyethylene glycol octylphenyl ether, liquids)

Part 1A. (2-Propanol)

Part 5. (2-Propanol)

**USA**

**Toxic Substances Control Act (TSCA) Section 8(b)**

All ingredients are listed on the TSCA Inventory.

**Additional USA Regulatory Lists**

Massachusetts Right To Know. (2-Propanol). (Dipropylene glycol monomethyl ether). (Benzyl acetate). (Benzaldehyde). (Ethyl acetate). (n-Amyl acetate)

New Jersey Right To Know. (Dipropylene glycol monomethyl ether). (Poly(oxy-1,2-ethanediyl), alpha-octyl- omega -hydroxy-). (Benzaldehyde). (2-Propanol). (n-Amyl acetate). (Ethyl acetate). (Benzyl acetate)

Pennsylvania Right To Know. (2-Propanol). (Poly(oxy-1,2-ethanediyl), alpha-octyl- omega -hydroxy-). (Dipropylene glycol monomethyl ether). (Benzyl acetate). (Benzaldehyde). (Ethyl acetate). (n-Amyl acetate)

Rhode Island Right To Know. (2-Propanol). (Benzyl acetate). (n-Amyl acetate). (Ethyl acetate)

California Proposition 65: Ethylene Oxide (CAS 75-21-8) Formaldehyde (CAS 50-00-0) 1,4-Dioxane (CAS 123-91-1) Acetaldehyde (CAS 75-07-0)

California Proposition 65 - Developmental Toxin: 1,4-Dioxane (CAS 123-91-1).

**SECTION 16. OTHER INFORMATION**

|                            |                   |                         |                        |
|----------------------------|-------------------|-------------------------|------------------------|
| <b>NFPA Rating</b>         | <b>Health - 1</b> | <b>Flammability - 0</b> | <b>Instability - 0</b> |
| <b>SDS Prepared By</b>     | Wayne Hegstrom    |                         |                        |
| <b>Phone No.</b>           | 405 682 2541      |                         |                        |
| <b>Date of Preparation</b> | March 27, 2015    |                         |                        |
| <b>Revision Indicators</b> | Not applicable.   |                         |                        |

---

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Page 07 of 07

Date of Preparation: March 27, 2015