

# CT66JCSS



33.25" x 23.63" x 23.5" (H x W x D)

Built-in undercounter refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, and fully wrapped stainless steel exterior

### Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Fully wrapped stainless steel cabinet and door bring true luxury under the counter

Improved temperature performance with our unique dual evaporator cooling

Zero degree freezer compartment

### Product Features:

100% CFC free	Environmentally friendly design without ozone-damaging chemicals
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Door storage	Keep tall bottles and condiments right on the door for convenient access
Fruit and vegetable crisper	Get the longest life and best taste out of produce by storing it in a convenient slide drawer
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Interior light	Automatically illuminates when you open the door
Adjustable thermostat	Dial thermostat located inside for easy temperature management
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Thin-line design	Our unique 24" wide models offer full capacity in a slim fit

**CT66JCSS Specifications:**

Overview	
Height	33.25"
Height to Hinge Cap	34.75"
Width	23.63"
Depth	23.5"
Depth with Handle	25.63"
Depth with door at 90°	45.63"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	143.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes

Thermostat Type	Dial
Fan Type	Exterior
Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

