

CT66JSSHADA



32" x 23.63" x 23.5" (H x W x D)

Freestanding ADA compliant refrigerator-freezer for general purpose use, w/dual evaporator cooling, cycle defrost, SS door, horizontal handle, white cabinet

Highlights:

32" height for use in ADA compliant settings

Improved temperature performance with our unique dual evaporator cooling

Professional look with a durable stainless steel wrapped door and sleek horizontal handle

Zero degree freezer compartment

Product Features:

ADA compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Slim counter height dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel door	Durable 304 grade wrapping
Professional horizontal handle	Thin 14mm diameter on stainless steel handle, mounted horizontally on the door
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Zero degree freezer	Static manual defrost freezer section offers more stability
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

CT66JSSHADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0

