

FF7BCSS



33.25" x 23.75" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use with stainless steel exterior, towel bar handle, and automatic defrost

Highlights:

Commercially approved for use in foodservice establishments

Complete stainless steel construction adds luxury to any setting

Automatic defrost minimizes user maintenance

Includes adjustable glass shelves for spill-proof storage

Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished cabinet	Allows the refrigerator to be used freestanding
Complete stainless steel construction	Durable design with lasting elegance
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Automatic defrost	Reduced user maintenance with automatic defrost
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices

FF7BCSS Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	34.75"
Width	23.75"
Depth	23.5"
Depth with Handle	25.25"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	148.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Height Adjustable	1
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"

Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

