

FF7LBI



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, with lock, flat door liner, automatic defrost operation and white exterior

Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Automatic defrost minimizes user maintenance

Factory-installed lock provides security you can count on

Product Features:

Commercially approved	ETL-S listed to NSF-7 commercial standards
Automatic defrost operation	Reduced user maintenance with automatic defrost
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Built-in capability	Make the best use of space by installing your refrigerator under the counter and flush with other cabinets
Fully finished white cabinet	Allows the refrigerator to be used freestanding
Front-mounted lock	Keyed lock for a secure interior
One piece seamless interior liner	Enjoy easy clean-up with a one piece liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

FF7LBI Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	104.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"

Compressor Step Depth

