

**REFRIGERATOR MANUFACTURER**  
**Turbo air**  
 more durable, efficient, beautiful

4184 E. Conant St.  
 Long Beach, CA 90808  
 Tel. 310-900-1000  
 Fax. 310-900-1077  
[www.turboairinc.com](http://www.turboairinc.com)

Project :	
Model # :	
Item # :	Qty :
Available W/H :	
Approval :	

## Diamond Show Case

Display Cases  
 Refrigerated Show Cases

**Model : CRT-77-2R**



Pass Through

### ≡ FEATURES & BENEFITS ≡

- **LED lighting interior display system**  
 Safety shielded 4 LED lighting system on every corner of the cabinet ensures a longer life and brighter lighting than fluorescent light bulbs, providing attractive, enhanced and shadow-free illumination.
- **Efficient refrigeration system**  
 Turbo Air's refrigerators are designed with oversized and balanced R-134A (CFC Free) refrigeration. These include efficient evaporators and condensers for faster cooling and greater efficiency.
- **Beautiful 4 sided glass cabinet allows visibility from all sides to optimize display effect**
- **Compact size and countertop design occupies minimum space but maximize impulse sales**
- **Great space efficiency is ideal for narrow space restaurants and convenience stores**
- **Elegant contemporary Euro design will enhance the interior and space decoration of any store**
- **Sturdy, clean stainless steel shelving**  
 Shelves are the most important part of cleanliness as they come in direct contact with food. After a while, PVC coated wire shelves may peel, rust and lead to unsanitary conditions. Only the Turbo Air Diamond Show Case uniquely provides stainless steel shelving.
- **Recommended operating conditions**  
 CRT models are designed to operate in environments where temperature & humidity do not exceed 75°F and 55% relative humidity.



Model	Swing Door	CU./FT.	# of Shelves	HP	AMPS	Crated Weight (lbs.)	L x D x H (inches)
<b>CRT-77-2R</b>	<b>2</b>	<b>3.0</b>	<b>3</b>	<b>2/9</b>	<b>2.6</b>	<b>90</b>	<b>163/4 x 167/8 x 381/2</b>

## Model : CRT-77-2R

ELECTRICAL DATA	
Voltage	115/60/1
Plug Type	Ⓜ NEMA 5-15P
Full Load Amperes	2.6
Compressor HP	2/9
Refrigerant	R-134A
Cord Length (ft.)	6.5
DIMENSIONAL DATA	
Net Capacity (cu. ft.)	3
Ext. Length Overall (in.)	16 <sup>3</sup> / <sub>4</sub> (425mm)
Ext. Depth Overall (in.)	16 <sup>7</sup> / <sub>8</sub> (427mm)
Ext. Height Overall (in.)	38 <sup>1</sup> / <sub>2</sub> (978mm)
Int. Length Overall (in.)	14 <sup>3</sup> / <sub>8</sub> (366mm)
Int. Depth Overall (in.)	13 <sup>1</sup> / <sub>8</sub> (335mm)
Int. Height Overall (in.)	25 (635mm)
Net Weight (lbs.)	82.5
Gross Weight (lbs.)	90
# of Shelves	3
Shelf Size (in.)	14 <sup>3</sup> / <sub>8</sub> x 12 <sup>3</sup> / <sub>4</sub>


Design and specifications subject to change without notice.  
Actual shipping weight may differ due to extra packing materials for product protection.

- **WARRANTY : 1 Year Parts and Labor Warranty**  
**Additional 4 Year Warranty on Compressor**


- **Self-contained system**
- **Door lock standard**

## PLAN VIEW


(unit : inch)



PLAN VIEW



FRONT VIEW



SIDE VIEW

Ver.201510



- Turbo Air : 800-627-0032
- GK : 800-500-3519
- Warranty : 800-381-7770
- AC : 888-900-1002