

FF7LBIIF



33.5" x 23.63" x 23.63" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, auto defrost w/lock, integrated frame for overlay panels, white cabinet

Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Customizable door front accepts full overlay panels for a seamless look that can blend into cabinetry

Factory-installed lock provides security you can count on

Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Integrated door frame	Customize the front by mounting an overlay panel over the door; seamless look can blend into other cabinetry with no exposed frame. Handle not included (panel size: 23 5/16" W x 28 1/4" H and at least 3/4" thick)
Factory installed lock	Keyed lock for a secure interior
Automatic defrost	Reduced user maintenance with automatic defrost
Adjustable shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Deep shelf space	Interior accommodates large trays up to 19 1/2" x 15 1/2"
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior

FF7LBIIF Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.63"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	108.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"

Compressor Step Depth

