

SCR1300



73" x 23.63" x 23.5" (H x W x D)

Commercial full-sized beverage merchandiser with automatic defrost in slim width

Highlights:

Full fluorescent light keeps all items on display to help increase impulse sales

Tropicalized glass door design keeps products well-preserved, even in hot temperatures

Ideal 24 inch footprint offers large capacity with storage all the way to the floor

Factory installed lock offers added security

Product Features:

Thin-line design	Limited space is no problem for our thin-line models, designed specifically for those hard-to-fit spots
Double pane tempered glass door	Tropicalized design protects contents from ambient hot temperatures
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Slide-out shelves with no clips for faster adjusting
Fluorescent lighting	Fully illuminates the interior on a convenient ON/OFF switch
Internal fan	Even circulation throughout the interior
Factory installed lock	Keyed lock for a secure interior
Factory reversible door	Unit ships RHD. Door swing can be specified upon order or reversed in the field with an optional left-hand hinge
Adjustable thermostat	Manage the interior temperature with ease and accuracy



SCR1300 Specifications:

Overview	
Height	73.0"
Width	23.63"
Depth	23.5"
Capacity	13.0 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	White
US Electrical Safety	ETL
Amps	5.4
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	220.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	5.2
High Side PSI	430.0
Low Side PSI	87.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	62.5"
Interior Width	19.25"
Interior Depth	17.25"
Compressor Step Height	8.0"
Compressor Step Width	19.25"
Compressor Step Depth	6.0"



