

# SCR600LADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant, Commercially listed freestanding glass door all-refrigerator with white cabinet and lock

## Highlights:

Commercially approved for use in food service establishments

32 inches high to meet ADA guidelines for lower counter height

Glass door provides heat-safe view of stored products

Factory installed lock provides security you can count on

## Product Features:

Commercially approved	ETL-S Listed and CalCode Compliant
ADA Compliant	32 inch height is designed to meet ADA guidelines for lower counter height
Factory installed lock	Keyed lock for a secure interior
Fully finished white cabinet	Allows the unit to be used freestanding
Double pane tempered glass door	Heat resistant design provides clear view of stored products
Automatic defrost	Reduced user maintenance with automatic defrost
One piece interior liner	Simple cleanup with a seamless liner that won't hold a mess in hidden crevices
Adjustable shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup
Interior light on rocker switch	Turn the light on when you need it and off when you're done with a convenient switch located behind the thermostat

**SCR600LADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.5"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	26.0"
Interior Width	20.75"
Interior Depth	17.5"
Compressor Step Height	6.0"
Compressor Step Width	20.75"

Compressor Step Depth

