

FF6L7SSHADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant commercial all-refrigerator for freestanding general purpose use, auto defrost with lock, SS wrapped door, horizontal handle, and white cabinet

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

Factory-installed lock provides security you can count on

Stainless steel door complete with sleek horizontal handle adds luxury to any setting

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator
Commercially approved	ETL-S listed to NSF-7 commercial standards
ADA compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Slim counter height dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel wrapped door	Durable design with lasting elegance
Professional horizontal handle	Brushed stainless steel handle with a thin 14mm diameter is mounted horizontally across the door for a sleek look
Factory installed lock	Keyed lock offers added security
Automatic defrost	Reduced maintenance with auto defrost system

FF6L7SSHADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	

Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

