

# SCR600LBIADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant commercially listed built-in undercounter glass door all-refrigerator with white cabinet and front lock

## Highlights:

Commercially approved for use in food service establishments

32 inch height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Factory installed lock provides security you can count on

## Product Features:

Commercially approved	ETL-S Listed and CalCode Compliant
ADA Compliant	32 inch height is designed to fit under ADA compliant counters
Factory installed lock	Keyed lock for a secure interior
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Fully finished white cabinet	Allows the unit to be used freestanding
Double pane tempered glass door	Heat resistant design provides clear view of stored products
Reversible door	Keep placement options flexible with a reversible door swing that is easy to switch when your arrangement changes
Automatic defrost	Reduced user maintenance with automatic defrost
One piece interior liner	Simple cleanup with a seamless liner that won't hold a mess in hidden crevices

**SCR600LBIADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.5"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	26.0"
Interior Width	20.75"
Interior Depth	17.5"
Compressor Step Height	6.0"

Compressor Step Width	20.75"
Compressor Step Depth	5.0"

