

SCUR20



81.5" x 31.25" x 31.25" (H x W x D)

Commercially approved frost-free all-refrigerator with digital thermostat, casters, lock, and right hand door swing

Highlights:

Commercially approved for use in foodservice establishments

True frost-free operation saves you maintenance by preventing icy buildup

Functional elegance with a sturdy towel bar handle in stainless steel

Digital thermostat with external readout for easy and accurate temperature control

Product Features:

Commercially approved	UL-S listed to NSF-7 for commercial use
Large capacity	Over 20 c.f. of storage space inside
Front mounted lock (located at bottom of door)	Keep contents secure with a key lock on the door
Digital thermostat	External temperature readout and precise temperature management with easy electronic controls
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Frost-free operation	No-frost convenience requires no manual defrosting
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Door storage	Store large bottles right on the door for easy access
Basket	More storage options with a slide-out basket at the bottom

SCUR20 Specifications:

Overview	
Height	81.5"
Width	31.25"
Depth	31.25"
Depth with door at 90°	60.25"
Capacity	20.5 cu.ft.
Defrost Type	Frost-Free
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	UL-S
Voltage/Frequency	115 V AC/60 Hz
Weight	265.0 lbs.
Shipping Weight	325.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	4
Full Door Shelf Qty	6
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Wheel Qty	4
Interior Light	Yes

