

FF7L



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, with front lock, automatic defrost operation and white exterior

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

Factory-installed lock provides security you can count on

Automatic defrost minimizes user maintenance

Product Features:

| | |
|--|---|
| ENERGY STAR certified commercial performance | Meets ENERGY STAR standards as a commercial refrigerator |
| Commercially approved | ETL-S listed to NSF-7 commercial standards |
| Fully finished white cabinet | Allows the refrigerator to be used freestanding |
| Front-mounted lock | Keyed lock for a secure interior |
| Automatic defrost operation | Reduced user maintenance with automatic defrost |
| One piece seamless interior liner | Enjoy easy clean-up with a one piece liner that won't hold a mess in hidden crevices |
| Hidden evaporator | Cold wall design with hidden evaporator and seamless interior |
| Deep shelf space | Interior accommodates large trays up to 19 1/2" x 15 1/2" |
| Adjustable shelves | Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up |

FF7L Specifications:

| Overview | |
|----------------------------|----------------|
| Height | 33.5" |
| Width | 23.63" |
| Depth | 23.5" |
| Depth with Handle | 25.13" |
| Depth with door at 90° | 46.13" |
| Capacity | 5.5 cu.ft. |
| Defrost Type | Automatic |
| Door | White |
| Cabinet | White |
| US Electrical Safety | UL |
| Canadian Electrical Safety | ULC |
| Sanitation | ETL-S |
| Amps | 1.3 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Shipping Weight | 102.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Refrigerator Features | |
| Door Swing | RHD |
| Reversible | Yes |
| Shelf Type | Wire |
| Shelf Qty | 3 |
| Adjustable Shelves | Yes |
| Thermostat Type | Dial |
| Refrigerant Type | R134a |
| Refrigerant Amount | 1.8 |
| High Side PSI | 285.0 |
| Low Side PSI | 70.0 |
| Level Legs Qty | 2 |
| Interior Light | Yes |
| Dimensions | |
| Interior Height | 27.75" |
| Interior Width | 20.0" |
| Interior Depth | 17.5" |
| Compressor Step Height | 7.0" |
| Compressor Step Width | 20.0" |
| Compressor Step Depth | 6.0" |

