

FF7LBISSHVADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant built-in undercounter all-refrigerator for general purpose or commercial use, auto defrost w/lock, SS door, thin handle, and white cabinet

Highlights:

32 inch height fits under lower ADA compliant counters

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel door and sleek handle add modern luxury to any setting

Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished white cabinet	Allows the refrigerator to be used freestanding
Factory installed lock	Keyed lock for a secure interior
Stainless steel door	Durable design with lasting elegance
Professional thin towel bar handle	Thin 14mm diameter on vertical stainless steel handle
Automatic defrost	Reduced user maintenance with automatic defrost

FF7LBISSHVADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.75"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	88.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	26.25"
Interior Width	21.0"
Interior Depth	17.75"

Compressor Step Height	5.5"
Compressor Step Width	21.0"
Compressor Step Depth	5.5"

