






TECHNICAL DRAWINGS



KGF-23



KGF-48



KGF-72



Glass Door Merchandiser Series Freezers



MODEL NUMBER	EXTERNAL DIMS (INCH) WxDxH	VOLTAGE / FREQUENCY	AMPS	STORAGE (CU-FT)	COMPRESSOR SIZE (HP)	TEMPERATURE	NET WEIGHT (LBS)	GROSS WEIGHT (LBS)	NEMA PLUG
KGF-23	26.8 x 31.9 x 79.5	115V / 60 Hz / 1	11.0	23	5/8	-10°F	302	353	5-15
KGF-48	53.9 x 31.9 x 79.5	115V / 60 Hz / 1	12.0	48	1	-10°F	477	567	5-20
KGF-72	81 x 31.9 x 79.5	115/208-230 / 60 Hz / 1	11.0	72	1-1/4	-10°F	706	829	L14-20



Warranty : 12 months parts & labor. Additional 48 months on compressor (part only)

KOOL-IT is a registered trademark of MVP Group. Specifications subject to change without notice.



Tel.: 514.737.9701 / Toll Free: 888.275.4538
 Fax: 514.342.3854 / Toll Free: 877.453.8832
 sales@mvpgroupcorp.com • www.mvpgroupcorp.com

Project Name:	
Location:	
Item:	Qty:
Model:	



KGF-48



KGF-23



KGF-72



Glass Door Merchandiser Series Freezers

Durable Design

- Modern & attractive appearance for any kitchen, C-Store, service station, etc.
- Black exterior baked enamel steel finish
- White interior baked enamel steel finish
- Interior base in stainless steel finish
- Heavy-duty polyethylene coated adjustable wire shelves
- Locking glass doors are ergonomically designed and self-closing with easy grab handles
- Plastic upper sign panel with lamp

Energy Efficient

- Entire cabinet structure engineered to the highest standards
- Built using foamed-in place high density CFC-free polyurethane insulation
- Unique triple pane heated glass doors with a layer of patented, transparent thermal insulating film applied between the glass layers
- CFC-free refrigerant with R-404a gas
- Magnetic door gaskets of one piece, providing a tight and efficient seal
- UL Approved and conforms to NSF 7 standards.

Superior Quality

- Positive air flow throughout with forced air movement throughout entire cabinet
- Freezers hold -10°F. for optimum storage & preservation of foods
- High efficiency evaporators with oversized condensing units on all models
- Digital temperature readout display with electronic thermostatic control
- LED interior lighting for total product display

