



**KUCR-27-1
KUCF-27-1**




**Dimensions (W" x D" x H")
27.5 x 30 x 36**

**KUCR-36-1
KUCF-36-1**




**Dimensions (W" x D" x H")
36.4 x 30 x 36**

**KUCR-48-2
KUCF-48-2**




**Dimensions (W" x D" x H")
48.3 x 30 x 36**

**KUCR-60-2
KUCF-60-2**



**Dimensions (W" x D" x H")
60.4 x 30 x 36**

**KUCR-72-3
KUCF-72-3**



**Dimensions (W" x D" x H")
72.4 x 30 x 36**



**Undercounter
Freezers & Refrigerators
KUCF / KUCR SERIES**

Project name:	
Location:	
Item:	Qty:
Model:	



27"
**KUCR-27-1
KUCF-27-1**



36"
**KUCR-36-1
KUCF-36-1**



48"
**KUCR-48-2
KUCF-48-2**



60"
**KUCR-60-2
KUCF-60-2**



72"
**KUCR-72-3
KUCF-72-3**

KOOL-IT is a registered trade mark of MVP Group.
Specifications subject to change without notice.



Tel.: 514.737.9701 / Toll Free: 888.275.4538
Fax: 514.342.3854 / Toll Free: 877.453.8832
sales@mvpgroupcorp.com www.mvpgroupcorp.com



Tel.: 514.737.9701 / Toll Free: 888.275.4538
Fax: 514.342.3854 / Toll Free: 877.453.8832
sales@mvpgroupcorp.com www.mvpgroupcorp.com

Refrigerators

Model Number	Capacity (cubic feet)	Number of Doors	Number of Shelves	HP	Amps	Refrigerant	Ship Weight (lbs.)	Ship Dimensions W" x D" x H"
KUCR-27-1	6.8	1	2	1/5	3.2	R134A	199	30x33.5x36
KUCR-36-1	9.2	1	2	1/5	3.2	R134A	247	38x33.5x36
KUCR-48-2	12.7	2	4	3/8	6.0	R134A	280	51x33.5x36
KUCR-60-2	16	2	4	3/8	6.0	R134A	333	63x33.5x36
KUCR-72-3	19.6	3	6	3/8	6.1	R134A	384	75x33.5x36

Freezers

KUCF-27-1	6.8	1	2	3/8	5.2	R134A	207	30x33.5x36
KUCF-36-1	9.2	1	2	3/8	5.2	R134A	256	38x33.5x36
KUCF-48-2	12.7	2	4	1/2	7.5	R404A	298	51x33.5x36
KUCF-60-2	16	2	4	1/2	7.5	R404A	351	63x33.5x36
KUCF-72-3	19.6	3	6	1/2	7.8	R404A	401	75x33.5x36

Voltage : 115/60/1 NEMA 5-15 plug

These units are designed for maximum performance in an air-conditioned area of 75°F ambient temperature and 55% relative humidity. There must be adequate ventilation at the top, sides & rear of the unit for proper operation.

Warranty : 18 months parts & labor. Additional 42 months on compressor (part only)



Energy Efficient

- Self-closing door with stay open feature
- Seals tight with magnetic vinyl gasket
- Foamed-in place high-density polyurethane insulated body, CFC-Free

Durable Design

- Created to endure the everyday stress of the commercial kitchen environment, to protect your long term investment and guarantee superior food preservation
- 2 height adjustable, heavy-duty, PE coated wire shelves per door
- Spring loaded, self closing doors
- Simple plug-in installation

Superior Quality

- Designed for mobility, reliability & efficiency in commercial kitchens
- 5" swivel castors with 2 front brakes
- 36" high working surface
- Easy grip handle(s)
- Entirely self-contained system
- Forced air refrigeration
- Automatic defrost system
- Easily adjustable shelf height
- Stainless Steel interior & exterior

KUCF Series Undercounter Freezers

- Temperature range : -1°F to -11°F

KUCR Series Undercounter Refrigerators

- Temperature range : 32°F to 45°F