



SPR627OSIF



34" x 23.63" x 23.5" (H x W x D)

Outdoor all-refrigerator for built-in use, with digital thermostat, panel-ready door, and black cabinet

Highlights:

ENERGY STAR certified commercial refrigerator

Designed and constructed for use in the outdoors

Flexible design allows built-in or freestanding use in 24" wide spaces

Customizable door front accepts full overlay panels for a seamless look that can blend into cabinetry

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator and meets DOE standards for residential use
Built-in capable	Front-breathing design lets you make the best use of space by installing your appliance under the counter
Panel-ready door	Integrated stainless steel door frame allows you to mount full overlay panels over the door to create a custom look that can blend into cabinetry with no exposed frame (panel size: 23 1/2" W x 30" H and at least 3/4" thick)
Frost-free operation	No-frost operation for minimum user maintenance
Digital thermostat	Electronic controls located inside the unit for precise temperature management
Recessed LED light	Elegant lighting with a convenient on/off switch on the control panel
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Internal fan	Fan-forced cooling ensures the unit is evenly cooled from top to bottom
Ground Fault Circuit Interrupter	Integrated GFCI exceeds U.L. requirements for safety by protecting your unit from shocks and circuit breaks



SPR627OSIF Specifications:

Overview	
Height	34.0"
Width	23.63"
Depth	23.5"
Depth with Handle	25.38"
Depth with door at 90°	45.63"
Capacity	4.6 cu.ft.
Defrost Type	Frost-Free
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	250.0kWh/year
Amps	0.8
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	110.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	0.99oz.
High Side PSI	270.0
Low Side PSI	105.0
Interior Light	Yes
Dimensions	
Interior Height	24.0"
Interior Width	19.25"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com