


Model 603357 TN (48x24x78)
 603357 GY (48x24x78)
 603357 BK (48x24x78)
























www.globalindustrial.com
 1-800-645-2986
 INDUSTRIAL STORAGE CABINET
 ASSEMBLY INSTRUCTION

Model 603357




CONTENTS


REF.	QTY.	DESCRIPTION	REF.	QTY.	DESCRIPTION
1	1	LEFT SIDE BACK PANEL	H1	3	M5 x 10mm ROUND PHILLIP HEAD SCREW 
2	1	RIGHT SIDE BACK PANEL	H2	3	5.25 mm PLAIN WASHER 
3	1	LEFT SIDE PANEL	H3	4	6.5 PLAIN WASHER 
4	1	RIGHT SIDE PANEL	H4	4	M6 x 19 mm ROUND PHILLIP HEAD SCREW 
5	1	SUPPORT BEAM	H5	6	HINGE PIN 
6	1	BOTTOM FRONT CHANNEL	H6	2	BUMPER 
7	1	BOTTOM FRONT KICK PLATE	H7	12	PLASTIC HINGE CAP 
8	1	BOTTOM SHELF	H8	16	SHELF CLIP 
9	1	TOP PANEL	H9	6	PLASTIC INSERT 
10	1	LEFT DOOR	H10	1	RIGHT HAND DOOR HANDLE 
11	1	RIGHT DOOR	H11	2	BACK PLATE 
12	4	SHELF	H12	4	5.5mm SPLIT WASHER 
13	4	GUSSET REINFORCEMENT PLATE	H13	4	M5 x 8mm ROUND PHILLIP HEAD SCREW 
			H14	1	COTTER PIN 
			H15	1	LOCK LATCH 
			H16	2	LOCKING ROD 
			H17	1	LOCKING BRACKET 
			H18	1	LEFT HAND DOOR HANDLE 
			H19	2	ROD GUIDE 
			H20	16	SHEET METAL 
				2	KEY 





WARNING.

1. USE 2 PEOPLE TO ASSEMBLE.
2. LAY PARTS ON SOFT SMOOTH NON-SCRATCH SURFACE.
3. DO NOT OVERLOAD SHELVES.
4. LOAD LOWER SHELVES FIRST.
5. DO NOT CLIMB OR STAND ON SHELVES.















LOCK ASSEMBLY



RIGHT DOOR ROD
ASSEMBLY



BEND 1 LEG OF
COTTER PIN WITH PLIERS.