

**Model  
DG250  
DG400**

## **Ductable Dual Fuel Heater**

*Perfect For  
Tent Applications*

*No Open Flame!  
No Problem!*

- Heavy-duty frame with wheels and lifting hook
- Changes from vapor propane to natural gas with a turn of a valve
- Low amp draw (5.0/8.5)
- Ductable up to 50'
- High CFM axial fan
- Air switch protected by 30 mesh filter
- Remote thermostat with 50' of cord (optional)
- Optional delay start relay
- Capable of continuous ventilation with thermostat control of heat
- See reverse side optional accessories

**heat  
wagon** 



### **SPECIFICATIONS**

<b>Model:</b>	<b>DG250</b>	<b>DG400</b>
Heat Input Btu/Hr	241,000/255,000	394,000/404,000
Fuel	Vapor Propane/Natural Gas	Vapor Propane/Natural Gas
Output (CFM)	2766	4120
Gas Consumption	2.6 GPH LP, 255 CFH NG	4.3 GPH LP, 404 CFH NG
Power Supply	120V, 5 amp	120V, 8 amp
Thermostat	On/Off	On/Off
Duct	50' (WD1625HT5)	50' (WD2025HT5)
Weight lbs.	139	233
Heater Dimensions	45"L x 31"W x 36"H	61"L x 34"W x 39"H

**heat wagon** 


Rev. 5-14

342 N. 400 E. Valparaiso, IN 46383  
219-464-8818 • 219-462-7985 • [www.heatwagon.com](http://www.heatwagon.com)

## Optional Accessories




**Digital Thermostat (with 50' cord)**  
Set Point Range: -30°F - 220°F  
Differential Range: 1° - 30°F  
**#ACC-DIGTHIDF**



**Duct Adapter for DG250**  
**#ACC-AR250**

**Duct Adapter for DG400**  
**#ACC-AR400**



### **LP Hose and Regulator Installation Kit**

Includes all the hardware needed for installing your heater to a vapor propane tank. It includes: POL fitting, high pressure regulator (reduces propane tank pressure to 10PSI), fittings for connecting regulator to 25' of 3/4" hose (CSA listed for propane and natural gas), second stage regulator (reduces line pressure of 10PSI to 9-14" water column outlet pressure), and 3/4" MNPT nipple for connection to heater, teflon tape also included.

**#ACC-INSTKIT**