

# HAND SEAMERS

They can bend sheet metal. Flatten it. And flat-out get the job done. 1/4" depth marks ensure an accurate bend, and a reinforced spring stands the test of time.



### Rugged and Durable

Stainless steel blades and a reinforced chrome silicon spring increase life and durability.



### Comfortable Grip

Over-molded handles reduce hand fatigue and won't slip or twist.



### Quick Identification

1/4" depth marks on the blades allow for quick bends.



### Seamer

For bending and flattening sheet metal.

## Product Specifications

Item Numbers	1891185	1891183	1891184
Product Descriptions	SMTHS3	SMTHS03	SMTHS6
Sizes	3"	3" Offset	6"
Capacity			
CRS	18ga	18ga	18ga
SS	22ga	22ga	22ga
<b>Dimensions</b>			
Length	9-3/4"	8-1/4"	10"
Width	3-1/8"	5"	6"
Height	7/8"	3-1/4"	3-1/2"
Weight	1.5 lbs.	1.4 lbs.	2.2 lbs.



1/4" depth marks on the blades allow for quick bends.



Locking latch.

3" Offset Hand Seamer  
1891183

6" Hand Seamer  
1891184

3" Hand Seamer  
1891185