


Sideline

63346 Heat Wave

PERFORMANCE FABRIC



© 2016 CF Stinson, Inc. all rights reserved.

Stinson®

Performance Summary

- Enhanced soil + stain resistance
- Enhanced abrasion resistance

Cleaning and Maintenance

Cleaning Code: **(W-S)** For water based stains use water based cleaning agents only, do not use solvents. For oil based stains use solvent cleaners only.

For additional cleaning information visit cfstinson.com

For complete specifications visit cfstinson.com

Dye lots may vary slightly.

* This term and any corresponding data refer to the typical performance in the tests indicated and should not be construed to imply the behavior of this or any other material under actual fire conditions.

Specifications



Content	100% Post-Industrial Recycled Polyester
Finish	Enhanced Soil and Stain Protection soil and stain protection
Weight	9.1 oz./lin. yd. ± 1.0 oz.
Width	54 inches
Repeat	Vertical: 13.75 inches, directional
Roll Size	55 yards

Performance Characteristics

Abrasion Resistance ASTM D-4157	Exceeds 100,000 double rubs - heavy duty
Break Strength ASTM D-5034	Warp: 260 lbs. min., Fill: 178 lbs. min.
Tear Strength ASTM D-2261	Warp: 25 lbs. min., Fill: 44 lbs. min.
Seam Slippage ASTM D-4034	Warp: 63 lbs. min., Fill: 36 lbs. min.
Brush Pilling ASTM D-3511	Class 5.0 min.
Colorfastness to Light AATCC-16	40 Hours, Class 4.0
Crocking AATCC-8	Dry: Class 4.0, Wet: Class 3.0

Flammability*

California 191-53 Technical Bulletin 117, Section E	Passed
UFAC	Class 1
NFPA 260	Class 1

May contribute to compliance with California Technical Bulletin 133 when used in conjunction with other suitable components.

This product is produced using 100% recycled fiber.



Stinson®

C.F. Stinson, Inc.
2849 Product Drive
Rochester Hills, MI 48309

P 800 841 6279
F 248 299 3884

cfstinson.com