

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Identity / Alternate Names

Orange Oil Furniture Polish

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use / Application Method

See Technical Data Sheet.

1.3. Details of the supplier of the safety data sheet

Company Name

Howard Products, Inc.
560 Linne Road
Paso Robles, CA 93446

CHEMTREC (USA)

(800) 424-9300

Customer Service: Howard Products, Inc.

EMERGENCY PHONE: 1-805-227-1000

FAX PHONE: 1-805-227-1007

2. Hazard identification of the product

2.1. Classification of the substance or mixture

Acute Tox. 4;H332

Harmful if inhaled.

Skin Irrit. 3;H316

Causes mild skin irritation. (Not adopted by US OSHA)

2.2. Label elements

Using the Toxicity Data listed in section 11 and 12 the product is labeled as follows.



Warning

H316 Causes mild skin irritation.

H332 Harmful if inhaled.

[Prevention]:

P261 Avoid breathing dust / fume / gas / mist / vapors / spray.

P271 Use only outdoors or in a well-ventilated area.

[Response]:

P304+312 IF INHALED: Call a POISON CENTER or doctor / physician if you feel unwell.

P332+313 If skin irritation occurs: Get medical advice / attention.

P340 Remove victim to fresh air and keep at rest in a position comfortable for breathing.

[Storage]:

No GHS storage statements

[Disposal]:

No GHS disposal statements

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

3. Composition/information on ingredients

This product contains the following substances that present a hazard within the meaning of the relevant State and Federal Hazardous Substances regulations.

Ingredient/Chemical Designations	Weight %	GHS Classification	Notes
Distillates (petroleum), hydrotreated heavy paraffinic CAS Number: 0064742-54-7	75 - 100	Carc. 1A;H350	[1]
Solvent naphtha (petroleum), heavy aliph CAS Number: 0064742-96-7	25 - 50	Asp. Tox. 1;H304	[1]
Orange oil CAS Number: 0008008-57-9	1.0 - 10	Flam. Liq. 3;H226 Skin Irrit. 2;H315	[1]

[1] Substance classified with a health or environmental hazard.

[2] Substance with a workplace exposure limit.

[3] PBT-substance or vPvB-substance.

*The full texts of the phrases are shown in Section 16.

4. First aid measures

4.1. Description of first aid measures

General

In all cases of doubt, or when symptoms persist, seek medical attention.
Never give anything by mouth to an unconscious person.

Inhalation

Remove to fresh air, keep patient warm and at rest. If breathing is irregular or stopped, give artificial respiration. If unconscious place in the recovery position and obtain immediate medical attention. Give nothing by mouth.

Eyes

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

Skin

Remove contaminated clothing. Wash skin thoroughly with soap and water or use a recognized skin cleanser.

Ingestion

If swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting.

4.2. Most important symptoms and effects, both acute and delayed

Overview

Exposure to solvent vapor concentrations from the component solvents in excess of the stated occupational exposure limits may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Symptoms include headache, nausea, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases, loss of consciousness.

Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin resulting in dryness, irritation and possible non-allergic contact dermatitis. Solvents may also be absorbed through the skin. Splashes of liquid in the eyes may cause irritation and soreness with possible reversible damage. See section 2 for further details.

Inhalation

Harmful if inhaled.

Skin

Causes mild skin irritation. (Not adopted by US OSHA)

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

5. Fire-fighting measures

5.1. Extinguishing media

Dry chemical, carbon dioxide, fog, foam.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition: High temperatures and fires may produce such toxic substances as carbon monoxide and carbon dioxide.

Avoid breathing dust / fume / gas / mist / vapors / spray.

5.3. Advice for fire-fighters

In the event of fire, wear full protective clothing and NIOSH Approved Self-contained breathing apparatus with full face piece operated in the pressure demand or other positive pressure mode. Move container from fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapors.

ERG Guide No. ----

6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Put on appropriate personal protective equipment (see section 8).

6.2. Environmental precautions

Do not allow spills to enter drains or watercourses.

Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

6.3. Methods and material for containment and cleaning up

Take the personal protective measures listed in section 8.

Contain and absorb spillage with non-combustible materials e.g. sand, earth, vermiculite. Place in closed containers outside buildings and dispose of according to the Waste Regulations. (See section 13).

Do not allow spills to enter drains or watercourses.

If drains, sewers, streams or lakes are contaminated, inform the local water company immediately. In the case of contamination of rivers, streams or lakes the Environmental Protection Agency should also be informed.

7. Handling and storage

7.1. Precautions for safe handling

See section 2 for further details. - [Prevention]:

7.2. Conditions for safe storage, including any incompatibilities

Handle containers carefully to prevent damage and spillage.

Incompatible materials: Acids, oxidizers, peroxides, and vinyl chloride.

See section 2 for further details. - [Storage]:

7.3. Specific end use(s)

No data available.

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

8. Exposure controls and personal protection

8.1. Control parameters

Exposure

CAS No.	Ingredient	Source	Value
0008008-57-9	Orange oil	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit
		Supplier	No Established Limit
0064742-54-7	Distillates (petroleum), hydrotreated heavy paraffinic	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit
		Supplier	No Established Limit
0064742-96-7	Solvent naphtha (petroleum), heavy aliph.;	OSHA	No Established Limit
		ACGIH	No Established Limit
		NIOSH	No Established Limit
		Supplier	No Established Limit

Contains mineral oil. The exposure limits for oil mist are 5 mg/m³ OSHA PEL and 10 mg/m³ ACGIH.

Carcinogen Data

CAS No.	Ingredient	Source	Value
0008008-57-9	Orange oil	OSHA	Select Carcinogen: No
		NTP	Known: No; Suspected: No
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No;
0064742-54-7	Distillates (petroleum), hydrotreated heavy paraffinic	OSHA	Select Carcinogen: No
		NTP	Known: No; Suspected: No
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No;
0064742-96-7	Solvent naphtha (petroleum), heavy aliph.;	OSHA	Select Carcinogen: No
		NTP	Known: No; Suspected: No
		IARC	Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No;

8.2. Exposure controls

Respiratory

If exposed to concentrations above the exposure limit use the appropriate respirators.

Eyes

Safety glasses with side shields

Skin

Wear overalls to keep skin contact to a minimum. Impervious rubber gloves

Engineering Controls

Provide adequate ventilation. Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and any vapor below occupational exposure limits suitable respiratory protection must be worn.

Other Work Practices

Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

See section 2 for further details. - [Prevention]:

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

9. Physical and chemical properties

Appearance	Orange Liquid
Odor	Orange
Odor threshold	Not Available
pH	Not Established
Melting point / freezing point	Not Established
Initial boiling point and boiling range	>400 F
Flash Point	326 F (163.33 C) Tag Closed Cup
Evaporation rate (Ether = 1)	< 1
Flammability (solid, gas)	Not Applicable
Upper/lower flammability or explosive limits	Lower Explosive Limit: Not Established Upper Explosive Limit: Not Established
Vapor pressure (Pa)	Not Established
Vapor Density	Not Established
Specific Gravity	0.86
Solubility in Water	Negligible
Partition coefficient n-octanol/water (Log Kow)	Not Measured
Auto-ignition temperature	Not Established
Decomposition temperature	Not Established
Viscosity (cSt)	Not Established Not Established
VOC %	Not Established

9.2. Other information

DMSO extract by IP346: Less than 3.0 wt % (mineral oil component only)

10. Stability and reactivity

10.1. Reactivity

Hazardous Polymerization will not occur.

10.2. Chemical stability

Stable under normal circumstances.

10.3. Possibility of hazardous reactions

No data available.

10.4. Conditions to avoid

Do not mix with other chemicals.

10.5. Incompatible materials

Acids, oxidizers, peroxides, and vinyl chloride.

10.6. Hazardous decomposition products

High temperatures and fires may produce such toxic substances as carbon monoxide and carbon dioxide.

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

11. Toxicological information

Acute toxicity

Exposure to solvent vapor concentrations from the component solvents in excess of the stated occupational exposure limits may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Symptoms include headache, nausea, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases, loss of consciousness.

Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin resulting in dryness, irritation and possible non-allergic contact dermatitis. Solvents may also be absorbed through the skin. Splashes of liquid in the eyes may cause irritation and soreness with possible reversible damage.

Ingredient	Oral LD50, mg/kg	Skin LD50, mg/kg	Inhalation Vapor LD50, mg/L/4hr	Inhalation Dust/Mist LD50, mg/L/4hr	Inhalation Gas LD50, ppm
Distillates (petroleum), hydrotreated heavy paraffinic - (64742-54-7)	5,000.00, Rat - Category: 5	No data available	No data available	2.18, Rat - Category: 4	No data available
Solvent naphtha (petroleum), heavy aliph - (64742-96-7)	2,500.00, Rat - Category: 5	No data available	No data available	No data available	No data available
Orange oil - (8008-57-9)	5,000.00, Rat - Category: 5	No data available	13.00, Rat - Category: 4	No data available	No data available

Note: When no route specific LD50 data is available for an acute toxin, the converted acute toxicity point estimate was used in the calculation of the product's ATE (Acute Toxicity Estimate).

Classification	Category	Hazard Description
Acute toxicity (oral)	---	Not Applicable
Acute toxicity (dermal)	---	Not Applicable
Acute toxicity (inhalation)	4	Harmful if inhaled.
Skin corrosion/irritation	3	Causes mild skin irritation. (Not adopted by US OSHA)
Serious eye damage/irritation	---	Not Applicable
Respiratory sensitization	---	Not Applicable
Skin sensitization	---	Not Applicable
Germ cell mutagenicity	---	Not Applicable
Carcinogenicity	---	Not Applicable
Reproductive toxicity	---	Not Applicable
STOT-single exposure	---	Not Applicable
STOT-repeated exposure	---	Not Applicable
Aspiration hazard	---	Not Applicable

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

12. Ecological information

12.1. Toxicity

No additional information provided for this product. See Section 3 for chemical specific data.

Aquatic Ecotoxicity

Ingredient	96 hr LC50 fish, mg/l	48 hr EC50 crustacea, mg/l	ErC50 algae, mg/l
Distillates (petroleum), hydrotreated heavy paraffinic - (64742-54-7)	5,000.00, Oncorhynchus mykiss	1,000.00, Daphnia magna	Not Available
Solvent naphtha (petroleum), heavy aliph.; - (64742-96-7)	Not Available	Not Available	Not Available
Orange oil - (8008-57-9)	Not Available	Not Available	Not Available

12.2. Persistence and degradability

There is no data available on the preparation itself.

12.3. Bioaccumulative potential

Not Measured

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This product contains no PBT/vPvB chemicals.

12.6. Other adverse effects

No data available.

13. Disposal considerations

13.1. Waste treatment methods

Do not allow into drains or water courses. Wastes and emptied containers should be disposed of in accordance with regulations made under the Control of Pollution Act and the Environmental Protection Act. Using information provided in this data sheet advice should be obtained from the Waste Regulation Authority, whether the special waste regulations apply.

14. Transport information

	DOT	IMO/IMDG	ICAO/IATA
14.1. UN number	Not Applicable	Not Applicable	Not Applicable
14.2. UN proper ship. name	Not Regulated	Not Regulated	Not Regulated
14.3. Transport hazard class(es)	DOT Hazard Class: N/A DOT Label: ---	IMDG: Not Applicable Sub Class: Not Applicable	Air Class: Not Applicable
14.4. Packing group	Not Applicable	Not Applicable	Not Applicable
14.5. Environmental hazards			
IMDG	Marine Pollutant: No		
14.6. Special precautions for user	No further information		
14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not Applicable		

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

15. Regulatory information

Regulatory Overview The regulatory data in Section 15 is not intended to be all-inclusive, only selected regulations are represented. All ingredients of this product are listed on the TSCA (Toxic Substance Control Act) Inventory or are not required to be listed on the TSCA Inventory.

WHMIS Classification Not Regulated

US EPA Tier II Hazards

Fire: No

Sudden Release of Pressure: No

Reactive: No

Immediate (Acute): Yes

Delayed (Chronic): No

EPCRA 311/312 Chemicals and RQs:

(No Product Ingredients Listed)

EPCRA 302 Extremely Hazardous :

(No Product Ingredients Listed)

EPCRA 313 Toxic Chemicals:

(No Product Ingredients Listed)

Proposition 65 - Carcinogens (>0.0%):

(No Product Ingredients Listed)

Proposition 65 - Developmental Toxins (>0.0%):

(No Product Ingredients Listed)

Proposition 65 - Female Repro Toxins (>0.0%):

(No Product Ingredients Listed)

Proposition 65 - Male Repro Toxins (>0.0%):

(No Product Ingredients Listed)

N.J. RTK Substances (>1%) :

(No Product Ingredients Listed)

Penn RTK Substances (>1%) :

(No Product Ingredients Listed)

Safety Data Sheet

Orange Oil Furniture Polish

SDS Revision Date:

08/20/2014

16. Other information

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. We accept no responsibility and disclaim all liability for any harmful effects which may be caused by exposure to our products. Customers/users of this product must comply with all applicable health and safety laws, regulations, and orders.

The full text of the phrases appearing in section 3 is:

H226 Flammable liquid and vapor.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H350 May cause cancer.

This is the first version in the GHS SDS format. Listings of changes from previous versions in other formats are not applicable.

Information contained herein was obtained from sources considered technically accurate and reliable. While every effort has been made to ensure full disclosure of product hazards, in some cases data is not available and is so stated. Since conditions of actual product use are beyond control of the supplier, it is assumed that users of this material have been fully trained according to the requirements of all applicable legislation and regulatory instruments. No warranty, expressed or implied, is made and supplier will not be liable for any losses, injuries or consequential damages which may result from the use of or reliance on any information contained in this document.

End of Document