


EVHC

High Lumen LED Emergency Light



U.S. Patents Pending

FEATURES

- High lumen output for high mounting height application
- Fully adjustable LED lamp-heads
- Long-Life Lithium Iron Phosphate Battery
- Temperature Range: 10 °C to 40 °C (50 °F to 104 °F)
- Listed to UL924 standards

ORDERING INFORMATION

EVHC				-	
MODEL	CAPACITY	SELF DIAGNOSTICS	FINISH	OPTIONS	
	6 6 Watts 12 12 Watts	Blank No Self-Diagnostics I Spectron® Self-Diagnostics ⁴	Blank White B Black	06L 6 Watt LED Lamps ¹ BC Battery Compartment ^{2,3}	

¹ Only available on EVHC with 12 watt capacity

² BC option only available in White Finish

³ BC option only available with EVHC6, EVHC6I, EVHC12 or EVHC12I, not available with EVHC12-06L or EVHC12I-06L

⁴ Not for use with 220-240VAC input

INPUT POWER CONSUMPTION

	INPUT V.	AMPS.	MAX. WATTS
EVHC6	120	0.028	2.30
	277	0.028	2.2
EVHC6I	120	0.023	2.30
	277	0.028	2.2
EVHC6I2	120	0.04	3.7
	277	0.04	4.0
EVHC6I2I	120	0.035	3.7
	277	0.04	4.0

Maintenance Mode Power Consumption -

120 VAC - 0.32W; 277VAC - 0.36W

The EVHC Series meets proposed California Energy Commission(CEC) requirements for limits on power consumption in maintenance mode with less than 0.5 watts.

ELECTRONICS

- 120 through 277 VAC, 50/60Hz input with intelligent 2 wire connection
- AC lockout and Low Voltage disconnect
- Battery re-charge within 24 hours
- Optional Self-Test/Self-Diagnostic circuitry
- -BC option adds ease of access battery compartment with polarity sensitive connector

MATCHING INDOOR REMOTE FIXTURES

WHITE DOUBLE
EVHCR2



BC option

