

GHD-20PFT, 20" GEAR HEAD TAPPING DRILL PRESS WITH POWER DOWN FEED 230V, 3PH

354026

Achieve precision drilling and tapping from a design that includes an easy-to-read internal depth gauge, three power down feeds, built-in spindle lock and calibrated fine down feed. JET backs this reliable combination drilling and tapping press with a Two Year Warranty.



FEATURES

- Heavy-duty design allows a variety of precision drilling and tapping applications
- Integrated tapping and reversing controls
- Large production table and T-slotted base
- Easy-to-read internal depth gauge
- Three power downfeed rates
- Calibrated fine downfeed built in
- TEFC motor
- Built-in spindle lock
- Head tilts left or right
- Easily accessible table raiser
- Drill chuck arbor
- Draw bar



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

GHD-20PFT, 20" GEAR HEAD TAPPING DRILL PRESS WITH POWER DOWN FEED 230V, 3PH

354026

SPECIFICATIONS

Style (Type)	Geared Head
Drills to Center of Circle (In.)	20
Drilling Capacity Cast Iron (In.)	1-1/2
Drilling Capacity Mild Steel (In.)	1-1/4
Tapping Capacity Cast Iron (In.)	15/16
Tapping Capacity Mild Steel (In.)	15/16
Column Diameter (In.)	4-1/2
Distance Column to Spindle (In.)	10
Range of Spindle Speeds (RPM)	Low - 120, 260, 460, 900, 1600, 3000; High - 60, 130, 230, 450, 800, 1500
Spindle Taper (In. x TPI)	MT-3
Spindle Travel (In.)	4-1/2
Spindle Distance to Base (In.)	44-5/16
Spindle Distance to Table (Max.) (In.)	30-1/2
Table Size (L x W) (In.)	21-3/4 x 19-1/2
Table Travel (In.)	25-1/2
T-Slots Number and Size (In.)	2 & 5/8
T-Slot Centers (In.)	9



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE